

**RoHS
Compliant**

Description

The product from multicomp-Pro is a one component, Non-drying thermally conductive paste. It contains NO SILICONE. It is based on a synthetic base-stock.

The filler content has been specifically chosen to enable close-proximity of heat sink to substrate and maintains good thermal conductivity at all temperatures.

It has excellent flow, thixotropic (Non- Slumping) yet still has flow through a small nozzle with minimum effort, excellent resistance to mould growth, excellent dielectric properties at all frequencies, non-corrosive to Cadmium and Zinc plate and is REACH & ROHS compliant: Contains NO SVHC's

Properties	Result	Unit
Colour	White	
Weight loss (24 hours @150°C)	0.52	%
Viscosity (@ 20°C)	200	Pa.s
Specific gravity (@ 20°C)	2.0	
Thermal Conductivity	0.91	W/m.k
Dielectric Strength	45	kV/mm
Dielectric Constant (@ 20°C)	2.5	100Hz
Dissipation factor (@ 20°C)	0.028	100Hz
Volume Resistivity	1×10^{15}	ohm.cm
Insulation resistance	1×10^{12}	ohms
Temperature range	-50 to +130	°C

Approvals

UL94 V-0	No
REACH (SVHC concentration)	Refer to SDS

Storage and Shelf Life

12 months at 25°C in Syringes. Store horizontally. "Product may settle during storage, if this occurs; dispense and discard any clear liquid"

Storage at 25 ±10°C is optimum for most products

Some systems are prone to settling due to high filler content and should be inverted every two to three weeks to reduce the accumulation of the fillers on the bottom of the containers.

Inventory should be rotated on a FIFO (first in, first out) basis.

Health and Safety

MP000433 health and safety data or our technical service department for individual/specific advice.

Part Number Table

Description	Part Number
Thermal Conductive Paste, White, Syringe, 30ml	MP000433
Thermal Conductive Paste, White, Container, 1kg	MP000434

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

multicomp^{PRO}