

## Section 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

Product name: MP000431 HARDENER

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

### 1.3. Details of the supplier of the safety data sheet

Company name: Premier Farnell

150 Armley Road

Leeds

LS12 2QQ

United Kingdom

Tel: + 44 (0) 870 129 8608

Fax: + 44 (0) 870 129 8611

Email: [information@premierfarnell.com](mailto:information@premierfarnell.com)

### 1.4. Emergency telephone number

Emergency tel: + 44 (0) 870 120 2530

(office hours only)

## Section 2: Hazards identification

### 2.1. Classification of the substance or mixture

Classification under CLP: Acute Tox. 4: H332; Skin Irrit. 2: H315; Eye Irrit. 2: H319; Resp. Sens. 1: H334; Skin Sens. 1: H317; Carc. 2: H351; STOT RE 2: H373; STOT SE 3: H335

Most important adverse effects: Harmful if inhaled. Causes skin irritation. Causes serious eye irritation. May cause allergy or asthma symptoms or breathing difficulties if inhaled. May cause an allergic skin reaction. Suspected of causing cancer ([inhalation]). May cause damage to organs ([respiratory system]) through prolonged or repeated exposure ([inhalation (dust/mist)]). May cause respiratory irritation.

### 2.2. Label elements

#### Label elements:

Hazard statements: H332: Harmful if inhaled.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H334: May cause allergy or asthma symptoms or breathing difficulties if inhaled.

H317: May cause an allergic skin reaction.

H351: Suspected of causing cancer ([inhalation]).

H373: May cause damage to organs ([respiratory system]) through prolonged or repeated exposure ([inhalation (dust/mist)]).

H335: May cause respiratory irritation.

# Safety Data Sheet

**Hazard pictograms:** GHS07: Exclamation mark  
GHS08: Health hazard



**Signal words:** Danger

**Precautionary statements:** P260: Do not breathe mist.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P304+P340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P342+P311: If experiencing respiratory symptoms: Call a POISON CENTER or doctor.

P302+P352: IF ON SKIN: Wash with plenty of water.

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P308+P313: IF exposed or concerned: Get medical advice/attention.

**Haz. ingredients (label):** DIPHENYLMETHANEDIISOCYANATE (ISOMERS & HOMOLOGUES); 4,4'-METHYLENEDIPHENYL DIISOCYANATE

## 2.3. Other hazards

**Other hazards:** Danger of serious damage to health by prolonged exposure.

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

DIPHENYLMETHANEDIISOCYANATE (ISOMERS & HOMOLOGUES)

EINECS	CAS	PBT / WEL	CLP Classification	Percent
618-498-9	9016-87-9	-	Carc. 2: H351; Acute Tox. 4: H332; Skin Irrit. 2: H315; STOT RE 2: H373; Eye Irrit. 2: H319; STOT SE 3: H335; Resp. Sens. 1: H334; Skin Sens. 1: H317; -: EUH204	50-70%

4,4'-METHYLENEDIPHENYL DIISOCYANATE - REACH registered number(s): 01-2119457014-47-XXXX

202-966-0	101-68-8	-	Carc. 2: H351; STOT RE 2: H373; Acute Tox. 4: H332; Skin Irrit. 2: H315; Eye Irrit. 2: H319; STOT SE 3: H335; Resp. Sens. 1: H334; Skin Sens. 1: H317	30-50%
-----------	----------	---	---	--------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. If irritation occurs or persists, seek medical attention. Transfer to hospital if necessary.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Do not induce vomiting. Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. If conscious, ensure the casualty sits or lies down. If unconscious, check for breathing and apply artificial respiration if necessary. If unconscious and breathing is OK, place in the recovery position. Transfer to hospital as soon as possible.

#### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact. May cause sensitisation in susceptible individuals.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be a feeling of tightness in the chest with shortness of breath. Exposure may cause coughing or wheezing. Potential potent asthmagen.

#### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Show this safety data sheet to the doctor in attendance. Eye bathing equipment should be available on the premises.

### Section 5: Fire-fighting measures

#### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

#### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

#### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

### Section 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

#### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

#### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Clean-up should be dealt with only by qualified personnel familiar with the specific substance.

**6.4. Reference to other sections**

Reference to other sections: Refer to section 8 of SDS.

**Section 7: Handling and storage**

**7.1. Precautions for safe handling**

**Handling requirements:** Ensure there is exhaust ventilation of the area. Avoid direct contact with the substance.  
Avoid the formation or spread of mists in the air.

**7.2. Conditions for safe storage, including any incompatibilities**

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.  
**Suitable packaging:** Must only be kept in original packaging.

**7.3. Specific end use(s)**

**Specific end use(s):** PC1: Adhesives, sealants.

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Hazardous ingredients:**

**DIPHENYLMETHANEDIISOCYANATE (ISOMERS & HOMOLOGUES)**

**Workplace exposure limits:** **Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	0.02 mg/m3	0.07 mg/m3	-	-

**4,4'-METHYLENEDIPHENYL DIISOCYANATE**

UK	0.02 mg/m3	0.07 mg/m3	-	-
----	------------	------------	---	---

**DNEL/PNEC Values**

**Hazardous ingredients:**

**4,4'-METHYLENEDIPHENYL DIISOCYANATE**

Type	Exposure	Value	Population	Effect
DNEL	Inhalation	50 ug/m3	Workers	Local
DNEL	Inhalation	100 ug/m3	Workers	Local
PNEC	Fresh water	1 mg/L	-	-
PNEC	Marine water	100 ug/L	-	-
PNEC	Microorganisms in sewage treatment	1 mg/L	-	-
PNEC	Soil (agricultural)	1 mg/kg	-	-

**8.2. Exposure controls**

**Engineering measures:** Ensure there is exhaust ventilation of the area.  
**Respiratory protection:** Self-contained breathing apparatus must be used in handling.

**Hand protection:** Impermeable gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Impermeable protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Brown

**Odour:** Characteristic odour

**Solubility in water:** Reacts with water.

**Viscosity:** Non-viscous

**Flash point°C:** 230

**Relative density:** 1.24

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### DIPHENYLMETHANEDIISOCYANATE (ISOMERS & HOMOLOGUES)

DERMAL	RBT	LD50	>9400	mg/kg
DUST/MIST	RAT	4H LC50	0.49	mg/l
ORAL	RAT	LD50	>10000	mg/kg

# Safety Data Sheet

## 4,4'-METHYLENEDIPHENYL DIISOCYANATE

DUST/MIST	RAT	4H LC50	0.368	mg/l
ORAL	RAT	LD50	9200	mg/kg

### Relevant hazards for product:

Hazard	Route	Basis
Acute toxicity (ac. tox. 4)	INH	Hazardous: calculated
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	INH DRM	Hazardous: calculated
Carcinogenicity	--	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated
STOT-repeated exposure	-	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact. May cause sensitisation in susceptible individuals.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be a feeling of tightness in the chest with shortness of breath. Exposure may cause coughing or wheezing. Potential potent asthmagen.

## Section 12: Ecological information

### 12.1. Toxicity

#### Hazardous ingredients:

#### DIPHENYLMETHANEDIISOCYANATE (ISOMERS & HOMOLOGUES)

Daphnia magna	48H EC50	>1640	mg/l
ZEBRAFISH (Brachydanio rerio)	96H LC50	>1000	mg/l

#### 4,4'-METHYLENEDIPHENYL DIISOCYANATE

Scenedesmus Subspicatus	72H ErC50	>1640	mg/l
ZEBRAFISH (Brachydanio rerio)	96H ErC50	>1000	mg/l

### 12.2. Persistence and degradability

**Persistence and degradability:** Not readily biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Reacts with water.

## 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

## 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Waste code number:** 08 05 01

**Disposal of packaging:** Arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH204: Contains isocyanates. May produce an allergic reaction.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H334: May cause allergy or asthma symptoms or breathing difficulties if inhaled.

H335: May cause respiratory irritation.

H351: Suspected of causing cancer ([inhalation]).

H373: May cause damage to organs ([respiratory system]) through prolonged or repeated exposure ([inhalation (dust/mist)]).

## Section 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

Product name: MP000431 RESIN

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

### 1.3. Details of the supplier of the safety data sheet

Company name: Premier Farnell

150 Armley Road

Leeds

LS12 2QQ

United Kingdom

Tel: + 44 (0) 870 129 8608

Fax: + 44 (0) 870 129 8611

Email: [information@premierfarnell.com](mailto:information@premierfarnell.com)

### 1.4. Emergency telephone number

Emergency tel: + 44 (0) 870 120 2530

(office hours only)

## Section 2: Hazards identification

### 2.1. Classification of the substance or mixture

Classification under CLP: This product has no classification under CLP.

### 2.2. Label elements

Label elements: This product has no label elements.

Haz. ingredients (label): ZEOLITES

### 2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

ZEOLITES

EINECS	CAS	PBT / WEL	CLP Classification	Percent
215-283-8	1318-02-1	Substance with a Community workplace exposure limit.	-	1-10%



## Section 4: First aid measures

### 4.1. Description of first aid measures

- Skin contact:** Wash immediately with plenty of soap and water.
- Eye contact:** Bathe the eye with running water for 15 minutes.
- Ingestion:** Do not induce vomiting. Wash out mouth with water. Consult a doctor.
- Inhalation:** Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

- Skin contact:** There may be mild irritation at the site of contact.
- Eye contact:** There may be irritation and redness.
- Ingestion:** There may be irritation of the throat.
- Inhalation:** No symptoms.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Not applicable.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Turn leaking containers leak-side up to prevent the escape of liquid. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Not applicable.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.

### 7.3. Specific end use(s)

**Specific end use(s):** PC1: Adhesives, sealants.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**ZEOLITES**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	10 mg/m3	-	4 mg/m3	-

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Not applicable.

**Respiratory protection:** Respiratory protection not required.

**Hand protection:** Protective gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Black

**Odour:** Barely perceptible odour

**Relative density:** 1.05

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

## 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

## 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

## 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

## 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids. Strong bases.

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Toxicity values:** No data available.

### Symptoms / routes of exposure

**Skin contact:** There may be mild irritation at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be irritation of the throat.

**Inhalation:** No symptoms.

## Section 12: Ecological information

### 12.1. Toxicity

**Hazardous ingredients:**

#### ZEOLITES

Daphnia magna	48H EC50	>1400	mg/l
FISH	96H LC50	>680	mg/l

### 12.2. Persistence and degradability

**Persistence and degradability:** No data available.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No data available.

### 12.4. Mobility in soil

**Mobility:** No data available.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

Other adverse effects: No data available.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Disposal of packaging:** Arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Part Number**

MP000431

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.