

Fabric label - EMLC (51X25)R YE - 0800558

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fabric label, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, lettering field size: 51 x 25 mm, Number of individual labels: 750

Your advantages

- ✓ The EMLC label consists of a fabric film with very low restoring forces
- ✓ Enables labels to be stuck over edges and curves
- ✓ When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences. The marking is even suitable for use under harsh industrial conditions.
- ✓ Labeling service: Phoenix Contact can custom-label all EMLC ... markers in accordance with your requirements

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356606936
Weight per Piece (excluding packing)	340.000 g
Custom tariff number	39269097
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	25 mm
Width (a)	51 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

General

Color	yellow
Components	free from silicone and halogen

Fabric label - EMLC (51X25)R YE - 0800558

Technical data

General

Material	PA
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	750
Number of individual labels per row	1
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146257 THERMOMARK S1.1
	5146231 THERMOMARK X1.2
	5146477 THERMOMARK ROLL
	5145313 THERMOMARK S1
	5145274 THERMOMARK X1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
	0829544 THERMOMARK-RIBBON 110 BU
	0829542 THERMOMARK-RIBBON 110 GN
	0829543 THERMOMARK-RIBBON 110 RD
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Burning behaviour	self-extinguishing
Foil strength	50 µm
Adhesive strength	20 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200

Fabric label - EMLC (51X25)R YE - 0800558

Classifications

eCl@ss

eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., width: 110 mm, color: black