

## Plastic label with drill hole - EMLP 30 (45X10)R YE CUS - 0802008

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plastic label with drill hole, can be ordered: by line, yellow, labeled according to customer specifications, mounting type: adhesive, lettering field size: 45 x 10 mm, Number of individual labels: 500

### Your advantages

- ✓ The EMLP 30 ... self-adhesive markers are particularly well suited to marking electrical buttons and indicator lamps on consoles and in control cabinets
- ✓ The markers meet the same standards as the engraved labels. They provide high-quality visuals.
- ✓ Quick and inexpensive marking with THERMOMARK ... roll printers from PHOENIX CONTACT



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 783118
GTIN	4046356783118
Weight per Piece (excluding packing)	1.990 g
Custom tariff number	49119900
Country of origin	Poland
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	46 mm
Width (a)	46 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

#### General

Color	yellow
-------	--------

# Plastic label with drill hole - EMLP 30 (45X10)R YE CUS - 0802008

## Technical data

### General

Components	free from silicone and halogen
Material	Polyester
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	500
Number of individual labels per row	1
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
	0804501 THERMOMARK ROLLMASTER 300
	0804663 THERMOMARK ROLLMASTER 600
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 60068-2-11:2000-02
Result of wipe resistance test	Test passed
Foil strength	50 µm
Adhesive strength	20 µm
Marking mounting type	adhesive

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137

## Plastic label with drill hole - EMLP 30 (45X10)R YE CUS - 0802008

### Classifications

#### eCl@ss

eCl@ss 8.0	27141137
eCl@ss 9.0	27400629

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504