

## Cable marker label - WML 46 (25X38)R - 0800067

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable marker label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, cable diameter: ≤ 46 mm, lettering field size: 25 x 38 mm, Number of individual labels: 250

### Your advantages

- ✓ High-quality labeling image created by thermal transfer printing
- ✓ The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- ✓ Resistant to solvents
- ✓ Quick and easy handling
- ✓ The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- ✓ The cable marker labels consist of a labeling field and a transparent protective foil



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 046356 563338 |
| GTIN                                 | 4046356563338   |
| Weight per Piece (excluding packing) | 390.000 g   |
| Custom tariff number                 | 39199080  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### Dimensions

|            |        |
|------------|--------|
| Length (b) | 182 mm |
| Width (a)  | 25 mm  |

#### Ambient conditions

|                                 |   |
|---------------------------------|---|
| Ambient temperature (operation) | -50 °C ... 110 °C   |
| Recommended storage conditions  | 23 °C / 50% relative humidity. Storage in poly bags is recommended prior to processing. |

# Cable marker label - WML 46 (25X38)R - 0800067

## Technical data

### General

|   |                                     |
|---|-------------------------------------|
| Color   | white                               |
| Base element material   | Vinyl film                          |
| Type  | Label                               |
| Components  | Silicone-free                       |
| Material  | PVC                                 |
| Wipe resistance   | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels   | 250                                 |
| Number of individual labels per row                                 | 2                                   |
| Adhesive  | Acrylic                             |
| Printability  | Thermal transfer                    |
| Device  | 1085260 THERMOMARK ROLL 2.0         |
|   | 0804501 THERMOMARK ROLLMASTER 300   |
|   | 0804663 THERMOMARK ROLLMASTER 600   |
| Ink ribbon  | 5145384 THERMOMARK-RIBBON 110       |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result  | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration   | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration   | 96 h                                |
| Salt spray testing result   | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Foil strength   | 50 µm                               |
| Adhesive strength   | 25 µm                               |
| Marking mounting type   | adhesive                            |

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |
|------------|---|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |

# Cable marker label - WML 46 (25X38)R - 0800067

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 6.0 | 27400400 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001530 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

## Approvals

### Approvals

Approvals

UL Recognized

Ex Approvals

### Approval details

|               |  |   |               |
|---------------|--|---|---------------|
| UL Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE MH 48542 |
|---------------|--|---|---------------|

## Cable marker label - WML 46 (25X38)R - 0800067

### Accessories

#### Accessories

#### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., width: 110 mm, color: black