

## PRODUCT DATA SHEET

# EVERBUILD® Triple Action Wood Treatment

KILLS AND PROTECTS AGAINST WOOD ROT, DECAY, FUNGI AND WOOD-BORING INSECTS.

### PRODUCT DESCRIPTION

EVERBUILD® Triple Action Wood Treatment takes care of all your wood treatment and preservation needs in one can. It is a solvent-free, low-odour solution based on Micro-fine active technology with added fungicides, algaecides and Permethrin to actively kill and protect against wood rot, decay, fungi and wood-boring insects. The fungicides and algaecides present in these formulations are finely dispersed so that wood penetration, and hence effectiveness, is much greater than standard wood preservation products.

EVERBUILD® Triple Action Wood Treatment is fast drying and non flammable, and application to wet timber is possible without loss of performance. It is specifically designed to deeply penetrate all wood and joinery to give long lasting protection from damage caused by wet rot, dry rot, decay, fungi and wood-boring insects/larvae.

### USES

For interior and exterior use on wood such as:

- Sheds and garages
- Fencing and farm buildings
- Roof beams and joists
- Garden furniture.
- Floorboards
- Window frames and doors.

### CHARACTERISTICS / ADVANTAGES

- Solvent-free formula
- Non flammable.
- Internal and external use.
- Can be applied to damp timbers.
- Penetrates deeply into the wood.
- Long lasting protection.
- Fast drying.

### PRODUCT INFORMATION

<b>Packaging</b>	1L, 2.5L, 5L and 25L tins
<b>Shelf Life</b>	Use within 2 years of manufacture.
<b>Storage Conditions</b>	Store between 5°C and 25°C in original containers away from children.

### APPLICATION INFORMATION

<b>Consumption</b>	Use as supplied (do not dilute). 1 litre will treat 3-4 square metres.
--------------------	------------------------------------------------------------------------

## APPLICATION INSTRUCTIONS

### **Precautionary Notes**

ALWAYS READ STATUTORY CONDITIONS RELATING TO USE BEFORE STARTING ANY WORK. Ensure good ventilation before applying and after application until the treatment has dried (HSE statutory 1 hour re-entry time or until surfaces are dry) NOTE: drying times will be extended in cold weather and if ventilation is restricted. Avoid contact with skin and eyes, remove any splashes immediately. Clean up spills immediately (to avoid staining) with warm soapy water.

In roof areas, felt under tiles must be protected from contact with the fluid. Roof insulation must be removed and only replaced when treated timbers are thoroughly dry. Water storage tanks must be covered. When treating flooring and joists, boards should be left up for as long as possible to assist ventilation/drying.

Switch off electrical circuits in the area being treated before, and until 48 hours after, treatment. PVC covered electrical wiring will not normally be affected, but it is recommended that any excess is wiped from cables wherever possible.

### **SUBSTRATE QUALITY / PRE-TREATMENT**

Ensure that surfaces are clean and free from paint varnish, stain, grease, bark or any other contaminants. Surfaces may be damp. If decay is already present, remove all decayed wood and replace with sound treated timber.

### **APPLICATION**

Shake well before use. Apply by brush, spray or dipping. Apply a minimum of two coats if brushing or spraying. The second coat should be applied after the first coat has dried. Pay particular attention to thoroughly soaking the end grain. Where possible, and for maximum protection, dip the end grains of the timber for a minimum of 3 minutes

NOTE: product is milky out of the can but dries clear

### **LIMITATIONS**

- Ready to use - do not dilute.
- For use only as specified as a surface biocide and wood preservative.
- Always use coarse rather than fine mist generators.
- Do not apply to surfaces on which food is prepared.
- Avoid contact with bitumen, roofing felt or plastics.
- External timbers must be overcoated to reduce environmental impact.
- Test on a small, inconspicuous area before treating larger areas.
- It is the user's responsibility to determine suitability for use. If in doubt, contact Technical Services Department for advice.

## VALUE BASE

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

## LOCAL RESTRICTIONS

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and uses.

## ECOLOGY, HEALTH AND SAFETY

For information and advice on the safe handling, storage and disposal of chemical products, users shall refer to the most recent Safety Data Sheet (SDS) containing physical, ecological, toxicological and other safety-related data.

STATUTORY CONDITIONS IN RELATION TO USE:  
FOR USE ONLY AS A WOOD PRESERVATIVE AND SURFACE BIOCIDES. 1 LITRE WILL TREAT 3-4 SQUARE METRES WHEN APPLIED BY BRUSH OR SPRAY. IF DIPPING, DIP FOR AT LEAST 3 MINUTES. READ ALL PRECAUTIONS BEFORE USE.

## LEGAL NOTES

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

**EVERBUILD BUILDING PRODUCTS LTD**

Site 41, Knowsthorpe Way  
Cross Green Industrial Estate  
Leeds, LS9 0SW  
Tel: 0113 240 3456  
Web: [www.everbuild.co.uk](http://www.everbuild.co.uk)  
Twitter: @everbuild

**SIKA LIMITED**

Watchmead  
Welwyn Garden City  
Hertfordshire, AL7 1BQ  
Tel: 01707 394444  
Web: [www.sika.co.uk](http://www.sika.co.uk)  
Twitter: @SikaLimited

**SIKA IRELAND LIMITED**

Ballymun Industrial Estate  
Ballymun  
Dublin 11, Ireland  
Tel: +353 1 862 0709  
Web: [www.sika.ie](http://www.sika.ie)  
Twitter: @SikaIreland

EVERBUILDTripleActionWoodTreatment-en-GBEVER-(05-2018)-1-1.pdf

Product Data Sheet  
EVERBUILD® Triple Action Wood Treatment  
May 2018, Version 01.01  
020405030100000004