



< List of part numbers with package codes >
ECASD60J227M010K00

Shape

L size	7.3 ±0.3mm
W size	4.3 ±0.2mm
T size	2.8 ±0.3mm
W1 size (max.)	2.4±0.2mm
S size	1.3±0.2mm
Size code in inch(mm)	2917(7343)

References







Packaging	Specifications	Minimum quantity
K	φ330mm Embossed taping	2500
Mass (typ.)		
1 piece		0.2g

Specifications

ESR (equivalent series resistance)	10mΩ
Capacitance	220μF ±20%
Rated voltage	6.3Vdc
Capacitance change rate	±20%
Operating temperature range	-40 to 105°C
Allowable Ripple Current	3.0Arms
Leakage Current	138.6μA

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.