


Clamps and Clips

P Clamps

HellermannTyton's P clamps are designed for locating wires, cables, and components in instruments, appliances, and electrical apparatus. These injection molded clamps are used for both internal and external installations. The inside edges are radiused to prevent cutting into cable insulation.



| Material Data | |
|-----------------------|---|
| Material | Polyamide 6.6 heat stabilized (PA66HS) |
| Color | Black |
| Operating Temperature | -40 °F to +221 °F (-40 °C to +105 °C) |
| Flammability | UL94 V2 |



Product Selection


| Article No. | Part No. | Type | Max. Ø Bundle | | Width (W) | | Mounting Hole Centers | | Mounting Hole Ø | | Radius | | Pkg. Qty. |
|-------------|------------------|------|---------------|---------------|---------------|--------------|-----------------------|----------|-----------------|----------|--------|--|-----------|
| | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | | | |
| 211-60000 | 211-60000 | H1P | .125" (3.2) | .393" (10.0) | .3346" (8.5) | .1654" (4.2) | .01969" (0.5) | 100 | | | | | |
| 211-60010 | 211-60010 | H1P | .125" (3.2) | .393" (10.0) | .3346" (8.5) | .1654" (4.2) | .01969" (0.5) | 1000 | | | | | |
| 211-60001 | 211-60001 | H2P | .196" (5.0) | .3937" (10.0) | .375" (9.5) | .1654" (4.2) | .03937" (1.0) | 100 | | | | | |
| 211-60020 | 211-60020 | H2P | .196" (5.0) | .3937" (10.0) | .375" (9.5) | .1654" (4.2) | .03937" (1.0) | 1000 | | | | | |
| 211-60002 | 211-60002 | H3P | .255" (6.5) | .3937" (10.0) | .3937" (10.0) | .1654" (4.2) | .03937" (1.0) | 100 | | | | | |
| 211-60040 | 211-60040 | H3P | .255" (6.5) | .3937" (10.0) | .3937" (10.0) | .1654" (4.2) | .03937" (1.0) | 1000 | | | | | |
| 211-60003 | 211-60003 | H4P | .314" (8.0) | .3937" (10.0) | .3937" (10.0) | .1654" (4.2) | .03937" (1.0) | 100 | | | | | |
| 211-60050 | 211-60050 | H4P | .314" (8.0) | .3937" (10.0) | .3937" (10.0) | .1654" (4.2) | .03937" (1.0) | 1000 | | | | | |
| 211-60005 | 211-60005 | H6P | .433" (11.0) | .3937" (10.0) | .5118" (13.0) | .1654" (4.2) | .03937" (1.0) | 100 | | | | | |
| 211-60061 | 211-60061 | H6P | .433" (11.0) | .3937" (10.0) | .5118" (13.0) | .1654" (4.2) | .03937" (1.0) | 1000 | | | | | |
| 211-60006 | 211-60006 | H7P | .492" (12.5) | .3937" (10.0) | .5512" (14.0) | .1654" (4.2) | .05906" (1.5) | 100 | | | | | |
| 211-60078 | 211-60078 | H7P | .492" (12.5) | .3937" (10.0) | .5512" (14.0) | .1654" (4.2) | .05906" (1.5) | 1000 | | | | | |
| 211-60007 | 211-60007 | H8P | .55" (14.0) | .3937" (10.0) | .5906" (15.0) | .1654" (4.2) | .05906" (1.5) | 100 | | | | | |
| 211-60090 | 211-60090 | H8P | .55" (14.0) | .3937" (10.0) | .5906" (15.0) | .1654" (4.2) | .05906" (1.5) | 1000 | | | | | |
| 211-60098 | 211-60098 | H9P | .629" (16.0) | .3937" (10.0) | .63" (16.0) | .1654" (4.2) | .05906" (1.5) | 1000 | | | | | |
| 211-60110 | 211-60110 | H10P | .688" (17.5) | .3937" (10.0) | .6693" (17.0) | .1654" (4.2) | .05906" (1.5) | 1000 | | | | | |
| 211-60120 | 211-60120 | H11P | .748" (19.0) | .3937" (10.0) | .7087" (18.0) | .1654" (4.2) | .07874" (2.0) | 1000 | | | | | |
| 211-60130 | 211-60130 | H12P | .807" (20.5) | .3937" (10.0) | .748" (19.0) | .1654" (4.2) | .07874" (2.0) | 1000 | | | | | |
| 211-60140 | 211-60140 | H13P | .866" (22.0) | .4724" (12.0) | .8071" (20.5) | .2047" (5.2) | .07874" (2.0) | 1000 | | | | | |
| 211-60150 | 211-60150 | H14P | .944" (24.0) | .4724" (12.0) | .8465" (21.5) | .2047" (5.2) | .07874" (2.0) | 1000 | | | | | |
| 211-60160 | 211-60160 | H15P | 1.003" (25.5) | .4724" (12.0) | .9055" (23.0) | .2047" (5.2) | .09843" (2.5) | 1000 | | | | | |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

T Clamps

T3 Series

T Series clamps are injection molded and designed for applications in electronics, automotive, aircraft, and appliance industries. The T3 series has a 3/8" wide contact area. All contact edges have a full radius for product protection, and sizes are clearly marked on each clamp.



| Material Data | |
|-----------------------|---|
| Material | Polyamide 6.6 (PA66) |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C) |
| Flammability | UL94 V2 |



US
File# E64139

| Product Selection | | | | | | | | |
|-----------------------------|--------------------|---------|---------------|-----------|-----------------------|----------------|-------|-----------|
| Article No. | Part No. | Type | Max. Ø Bundle | Width (W) | Mounting Hole Centers | Wall Thickness | Color | Pkg. Qty. |
| | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | | |
| T Clamps - T3 Series | | | | | | | | |
| 211-00132 | T3D012510M4 | T3D0125 | .125" | .375" | .329" | .050" | White | 1000 |
| 211-00131 | T3D01250M4 | T3D0125 | (3.2) | (9.5) | (8.4) | (1.3) | Black | 1000 |
| 211-00158 | T3D018710M4 | T3D0187 | .188" | .375" | .430" | .050" | White | 1000 |
| 211-00133 | T3D01870M4 | T3D0187 | (4.7) | (9.5) | (10.9) | (1.3) | Black | 1000 |
| 211-00135 | T3D025010M4 | T3D0250 | .250" | .375" | .410" | .050" | White | 1000 |
| 211-00134 | T3D02500M4 | T3D0250 | (6.3) | (9.5) | (10.4) | (1.3) | Black | 1000 |
| 211-00137 | T3D031210M4 | T3D0312 | .313" | .375" | .495" | .050" | Black | 1000 |
| 211-00136 | T3D03120M4 | T3D0312 | (7.9) | (9.5) | (12.6) | (1.3) | Black | 1000 |
| 211-00139 | T3D037510M4 | T3D0375 | .375" | .375" | .595" | .050" | White | 1000 |
| 211-00138 | T3D03750M4 | T3D0375 | (9.5) | (9.5) | (15.1) | (1.3) | Black | 1000 |
| 211-00140 | T3D043710M4 | T3D0437 | .438" | .375" | .574" | .050" | White | 1000 |
| 211-00146 | T3D04370M4 | T3D0437 | (11.1) | (9.5) | (14.6) | (1.3) | Black | 1000 |
| 211-00141 | T3D050010M4 | T3D0500 | .500" | .375" | .605" | .050" | White | 1000 |
| 211-00142 | T3D05000M4 | T3D0500 | (12.7) | (9.5) | (15.4) | (1.3) | Black | 1000 |
| 211-00143 | T3D056210M4 | T3D0562 | .563" | .375" | .606" | .050" | White | 1000 |
| 211-00159 | T3D05620M4 | T3D0562 | (14.3) | (9.5) | (15.4) | (1.3) | Black | 1000 |
| 211-00145 | T3D062510M4 | T3D0625 | .625" | .375" | .678" | .050" | White | 1000 |
| 211-00144 | T3D06250M4 | T3D0625 | (15.8) | (9.5) | (17.2) | (1.3) | Black | 1000 |


Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Clamps and Clips

T Clamps

T5 Series

T Series clamps are injection molded and designed for applications in electronics, automotive, aircraft, and appliance industries. The T5 series provides a full 1/2" wide contact area. All contact edges have a full radius for product protection, and sizes are clearly marked on each clamp.



| Material Data | |
|-----------------------|---|
| Material | Polyamide 6.6 (PA66) |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C) |
| Flammability | UL94 V2 |




CALUS
File# E64139

| Product Selection | | | Max. Ø Bundle | Width (W) | Mounting Hole Centers | Wall Thickness | Color | Pkg. Qty. |
|-----------------------------|--------------------|---------|---------------|-----------|-----------------------|----------------|-------|-----------|
| Article No. | Part No. | Type | in. (mm) | in. (mm) | in. (mm) | in. (mm) | | |
| T Clamps - T5 Series | | | | | | | | |
| 211-00117 | T5D012510M4 | T5D0125 | .125" | .500" | .315" | .050" | White | 1000 |
| 211-00129 | T5D01250M4 | T5D0125 | (3.2) | (12.7) | (9.1) | (1.3) | Black | 1000 |
| 211-00118 | T5D018710M4 | T5D0187 | .188" | .500" | .425" | .050" | White | 1000 |
| 211-00130 | T5D01870M4 | T5D0187 | (4.7) | (12.7) | (10.8) | (1.3) | Black | 1000 |
| 211-00109 | T5D025010M4 | T5D0250 | .250" | .500" | .410" | .050" | White | 1000 |
| 211-00123 | T5D2500M4 | T5D0250 | (6.3) | (12.7) | (11.7) | (1.3) | Black | 1000 |
| 211-00110 | T5D031210M4 | T5D0312 | .313" | .500" | .500" | .050" | White | 1000 |
| 211-00147 | T5D02500M4 | T5D0312 | (7.9) | (12.7) | (12.7) | (1.3) | Black | 1000 |
| 211-00111 | T5D037510M4 | T5D0375 | .375" | .500" | .530" | .050" | White | 1000 |
| 211-00124 | T5D03750M4 | T5D0375 | (9.5) | (12.7) | (13.4) | (1.3) | Black | 1000 |
| 211-00148 | T5D043710M4 | T5D0437 | .438" | .500" | .560" | .050" | White | 1000 |
| 211-00149 | T5D04370M4 | T5D0437 | (11.1) | (12.7) | (14.2) | (1.3) | Black | 1000 |
| 211-00112 | T5D050010M4 | T5D0500 | .500" | .500" | .595" | .050" | White | 1000 |
| 211-00125 | T5D05000M4 | T5D0500 | (12.7) | (12.7) | (15.1) | (1.3) | Black | 1000 |
| 211-00113 | T5D056210M4 | T5D0562 | .563" | .500" | .606" | .050" | White | 1000 |
| 211-00150 | T5D05620M4 | T5D0562 | (14.3) | (12.7) | (15.4) | (1.3) | Black | 1000 |
| 211-00114 | T5D062510M4 | T5D0625 | .625" | .500" | .655" | .050" | White | 1000 |
| 211-00126 | T5D06250M4 | T5D0625 | (15.8) | (12.7) | (16.6) | (1.3) | Black | 1000 |
| 211-00115 | T5D075010M4 | T5D0750 | .750" | .500" | .780" | .050" | White | 1000 |
| 211-00127 | T5D07500M4 | T5D0750 | (19.0) | (12.7) | (19.8) | (1.3) | Black | 1000 |
| 211-00116 | T5D087510H4 | T5D0875 | .875" | .500" | .845" | .050" | White | 500 |
| 211-00128 | T5D08750H4 | T5D0875 | (22.2) | (12.7) | (21.4) | (1.3) | Black | 500 |
| 211-00119 | T5D100010H4 | T5D1000 | 1.000" | .500" | .910" | .050" | White | 500 |
| 211-00151 | T5D10000H4 | T5D1000 | (25.4) | (12.7) | (23.1) | (1.3) | Black | 500 |
| 211-00120 | T5D112510H4 | T5D1125 | 1.125" | .500" | .970" | .050" | White | 500 |
| 211-00152 | T5D11250H4 | T5D1125 | (125) | (12.7) | (24.6) | (1.3) | Black | 500 |
| 211-00153 | T5D118710H4 | T5D1187 | 1.188" | .500" | 1.000" | .050" | White | 500 |
| 211-00154 | T5D11870H4 | T5D1187 | (30.1) | (12.7) | (25.4) | (1.3) | Black | 500 |
| 211-00121 | T5D12500F4 | T5D1250 | 1.250" | .500" | 1.060" | .050" | White | 250 |
| 211-00155 | T5D125010F4 | T5D1250 | (31.7) | (12.7) | (26.9) | (1.3) | Black | 250 |
| 211-00157 | T5D137510F4 | T5D1375 | 1.375" | .500" | 1.125" | .050" | White | 250 |
| 211-00156 | T5D13750F4 | T5D1375 | (34.9) | (12.7) | (28.9) | (1.3) | Black | 250 |
| 211-00122 | T5D150010F4 | T5D1500 | 1.500" | .500" | 1.190" | .050" | White | 250 |
| | | | (38.1) | (12.7) | (30.2) | (1.3) | | |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Screw Mount Cable Clips

Available in three sizes, HellermannTyton screw mount clips offer quick, snap-in action. These clips allow for easy release for wiring changes or replacements, saving both time and money.



| Material Data | | RoHS |
|-----------------------|--------------------------------------|------|
| Material | Polyacetal (POM) | |
| Color | Black | |
| Operating Temperature | -40 °F to +194 °F (-40 °C to +90 °C) | |
| Flammability | UL94 HB | |


| Product Selection | | | | | | | | | |
|-------------------|----------|------|--------------|-------------|-------------|---------------|-----------------|----------------|-----------|
| Article No. | Part No. | Type | Length (L) | Length (L2) | Width (W) | Max. Ø Bundle | Mounting Hole Ø | Wall Thickness | Pkg. Qty. |
| | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 211-70200 | D10H4 | 8D10 | .67" (17.0) | .31" (8.0) | .60" (15.0) | .40" (10.0) | .31" (8.0) | .08" (2.0) | 500 |
| 211-70203 | D15L4 | 8D15 | 1" (25.0) | .40" (10.0) | .60" (15.0) | .60" (15.0) | .31" (8.0) | .08" (2.0) | 200 |
| 211-70204 | D20L4 | 8D20 | 1.10" (28.0) | .40" (10.0) | .60" (15.0) | .78" (20.0) | .31" (8.0) | .10" (2.5) | 200 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Series 52 Clamps

Series 52 clamps offer a fast, convenient, low cost method of routing wires and cables. The easy to install adhesive system eliminates the time and expense of drilling holes. Ideal for economical wire and cable retention applications. Extruded from PVC. For bundles up to 1".

| Material Data | | RoHS |
|-----------------------|--------------------------------------|------|
| Material | PVC (Polyvinylchloride) | |
| Color | Gray | |
| Operating Temperature | -20 °F to +150 °F (-28 °C to +65 °C) | |
| Flammability | UL94 V0 (excluding adhesive) | |




| Product Selection | | | | | | | | | |
|-------------------|-----------|---------|---------------|---------------|----------------|--------------|--------------|---------------|-----------|
| Article No. | Part No. | Type | Min. Ø Bundle | Max. Ø Bundle | Length (L) | Width (W) | Height (H) | Height (H2) | Pkg. Qty. |
| | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-00243 | 52-0500C2 | 52-0500 | .25" (6.35) | .5" (12.7) | .75" (19.1) | .75" (19.1) | .433" (11) | .75" (19.10) | 100 |
| 151-00244 | 52-0500M4 | 52-0500 | .25" (6.35) | .5" (12.7) | .75" (19.1) | .75" (19.1) | .433" (11) | .75" (19.10) | 1000 |
| 151-00245 | 52-0250C2 | 52-0250 | .125" (3.18) | .25" (6.35) | .5" (12.7) | .5" (12.7) | .31" (7.87) | .45" (11.43) | 100 |
| 151-00246 | 52-0250M4 | 52-0250 | .125" (3.18) | .25" (6.35) | .5" (12.7) | .5" (12.7) | .31" (7.87) | .45" (11.43) | 1000 |
| 151-00247 | 52-0750H4 | 52-0750 | .5" (12.7) | .75" (19.1) | 1.125" (28.57) | 1" (25.4) | .61" (15.49) | 1.05" (26.70) | 500 |
| 151-00248 | 52-0750K2 | 52-0750 | .5" (12.7) | .75" (19.1) | 1.125" (28.57) | 1" (25.4) | .61" (15.49) | 1.05" (26.70) | 50 |
| 151-00249 | 52-1000H4 | 52-1000 | .75" (19.1) | 1" (25.4) | 1.5" (38.1) | 1.25" (31.8) | .74" (18.8) | 1.35" (34.30) | 500 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Clamps and Clips

Series 12 Cable Clips

HellermannTyton's Series 12 cable clamps feature an exclusive quick lock/release for simplified wire installations. The easy to install adhesive system allows for faster assembly. Series 12 clamps can be used for various electrical, electronic and electromechanical applications. For bundles up to 3/4".



| Material Data | |
|-----------------------|---|
| Material | Polyamide 6.6 (PA66) |
| Color | Gray |
| Operating Temperature | -40 °F to +150 °F (-40 °C to +65 °C) |
| Flammability | UL94 V2 (excluding adhesive) |




| Product Selection | | | | | | | | | | |
|-------------------|------------------|---------|---------------|------------|----------|-----------|----------|------------|----------|-----------|
| Article No. | Part No. | Type | Max. Ø Bundle | Length (L) | | Width (W) | | Height (H) | | Pkg. Qty. |
| | | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-00274 | 12-0188C2 | 12-0188 | .188" | .62" | .74" | .39" | .335" | .08" | 100 | |
| 151-00275 | 12-0188M4 | 12-0188 | (4.78) | (15.75) | (18.8) | (9.91) | (8.51) | (18.67) | 1000 | |
| 151-00268 | 12-0250C2 | 12-0250 | .25" | .87" | 1" | .63" | .42" | .100" | 100 | |
| 151-00269 | 12-0250M4 | 12-0250 | (6.35) | (22.1) | (25.4) | (16) | (10.67) | (2.54) | 1000 | |
| 151-00270 | 12-0375C2 | 12-0375 | .375" | 1" | 1" | .63" | .5" | .11" | 100 | |
| 151-00271 | 12-0375M4 | 12-0375 | (9.53) | (25.4) | (25.4) | (16) | (12.7) | (2.8) | 1000 | |
| 151-00272 | 12-500C2 | 12-0500 | .5" | 1.21" | 1" | .64" | .68" | .11" | 100 | |
| 151-00273 | 12-500M4 | 12-0500 | (12.70) | (30.7) | (25.4) | (16.26) | (17.27) | (2.79) | 1000 | |
| 151-00276 | 12-0750C2 | 12-0750 | .75" | 1.45" | 1.15" | .64" | .99" | .125" | 100 | |
| 151-00277 | 12-0750H4 | 12-0750 | (19.10) | (36.83) | (29.21) | (16.26) | (25.15) | (3.18) | 500 | |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Series 22 Clamps

Series 22 round clamps are an attractive, low cost alternative recommended where the exceptionally high performance series 12 clamps are not needed. Series 22 wire clamps are constructed of precision extruded PVC and easy to install adhesive system. They provide the same basic advantages as the series 12 clamps. For bundles up to 3/4".

| Material Data | |
|-----------------------|---|
| Material | PVC (Polyvinylchloride) |
| Color | Black |
| Operating Temperature | -20 °F to +150 °F (-28 °C to +65 °C) |
| Flammability | UL94 V0 (excluding adhesive) |




| Product Selection | | | | | | | |
|-------------------|------------------|---------|---------------|------------|-----------|------------|-----------|
| Article No. | Part No. | Type | Max. Ø Bundle | Length (L) | Width (W) | Height (H) | Pkg. Qty. |
| | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-00250 | 22-0188M4 | 22-0188 | .188" | .750" | 1" | .337" | 1000 |
| 151-00251 | 22-0250M4 | 22-0250 | .250" | 1.02" | 1" | .420" | 1000 |
| 151-00252 | 22-0375M4 | 22-0375 | .375" | 1" | 1" | .551" | 1000 |
| 151-00253 | 22-0500M4 | 22-0500 | .500" | 1.25" | 1" | .701" | 1000 |
| 151-00254 | 22-0625H4 | 22-0625 | .625" | 1.25" | 1.25" | .801" | 500 |
| 151-00255 | 22-0750C2 | 22-0750 | .750" | 1.5" | 1.5" | .966" | 100 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Series 32 Clamps

The series 32 clamps have a narrower width than the series 22 clamps, making them compact and ideal for installations in cramped quarters. Series 32 wire clamps are constructed of precision extruded PVC and easy to install adhesive system. They provide the same basic advantages as the series 12 clamps. For bundles up to 3/4".



| Material Data | |
|-----------------------|---|
| Material | PVC (Polyvinylchloride) |
| Color | Black |
| Operating Temperature | -20 °F to +150 °F (-28 °C to +65 °C) |
| Flammability | UL94 V0 (excluding adhesive) |



| Product Selection | | | Max. Ø Bundle | Length (L) | Width (W) | Height (H) | Pkg. Qty. |
|-------------------|------------------|---------|---------------|---------------|---------------|---------------|-----------|
| Article No. | Part No. | Type | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-00256 | 32-0188M4 | 32-0188 | .188" (4.76) | .750" (19.05) | .500" (12.7) | .337" (8.56) | 1000 |
| 151-00257 | 32-0250M4 | 32-0250 | .250" (6.35) | 1.02" (25.91) | .500" (12.7) | .420" (10.67) | 1000 |
| 151-00258 | 32-0375M4 | 32-0375 | .375" (9.53) | 1" (25.4) | .500" (12.7) | .551" (14) | 1000 |
| 151-00259 | 32-0500M4 | 32-0500 | .500" (12.7) | 1.25" (31.75) | .500" (12.7) | .701" (17.81) | 1000 |
| 151-00260 | 32-0625H4 | 32-0625 | .625" (15.87) | 1.25" (31.75) | .625" (15.87) | .801" (20.35) | 500 |
| 151-00261 | 32-0750C2 | 32-0750 | .750" (19.05) | 1.5" (38.1) | .750" (19.05) | .966" (24.54) | 100 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.


RB Clips

RB self-adhesive clips are ideal for cable and pipe bundles. Bundles are easily snapped into or out of clips. The RB clips suit diameters of 1/8", 5/16", and 1/2".



Adhesive clips come in pairs connected together on adhesive liner.

| Material Data | |
|-----------------------|---|
| Material | Polyamide 6.6 (PA66) |
| Color | Natural |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C) |
| Flammability | UL94 V2 (excluding adhesive) |





| Product Selection | | | Max. Ø Bundle | Length (L) | Width (W) | Height (H) | Pkg. Qty. |
|-------------------|---------------|------|---------------|---------------|---------------|-------------|-----------|
| Article No. | Part No. | Type | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-14005 | RB5H4 | RB5 | .1969" (5.0) | .75" (19.0) | .75" (19.0) | .24" (6.0) | 500 |
| 151-13608 | RB8L4 | RB8 | .315" (8.0) | 1" (25.0) | 1" (25.0) | .45" (11.5) | 200 |
| 151-00506 | RB14L4 | RB14 | .512" (14.0) | 1.307" (33.2) | 1.079" (27.4) | .63" (16.0) | 200 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

TSR Adhesive Clips

TSR clips are designed from HellermannTyton's TSR surface raceway. The co-extruded hinge offers almost unlimited access to wire and cable without deformation or signs of wear often found when using many conventional clips. Designed for applications that require repeated access to the wire and cable, TSR clips are easy to open and close quickly and repeatedly. The tough, rubber-based adhesive allows for permanent bond to most surfaces. TSR clips are especially useful in prototype construction, engineering labs, or where constant changes are necessary.



| Material Data | |
|---------------|------------------------------|
| Material | PVC (Polyvinylchloride) |
| Color | Ivory |
| Flammability | UL94 V0 (excluding adhesive) |




| Product Selection | | | Max. Ø Bundle | Length (L) | Width (W) | Width (W2) | Height (H) | Pkg. Qty. |
|-------------------|-------------------|----------|---------------|---------------|--------------|---------------|--------------|-----------|
| Article No. | Part No. | Type | | | | | | |
| 151-00278 | SRCI0500C2 | SRCI0500 | .50" (12.7) | .755" (19.17) | .84" (21.3) | .75" (19.05) | .50" (12.7) | 100 |
| 151-00279 | SRCI0750C2 | SRCI0750 | .75" (19.05) | 1.25" (31.75) | 1.36" (34.5) | 1.25" (31.75) | .75" (19.05) | 100 |
| 151-00280 | SRCI1000K2 | SRCI1000 | 1.0" (25.4) | 1.75" (44.45) | 1.88" (47.8) | 1.75" (44.45) | 1.0" (25.4) | 50 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Low Profile Clips

Low profile clips are self-adhesive and ideal for use with ribbon cable. Side gripping fingers exert a firm hold but allow for easy removal when required.



| Material Data | |
|-----------------------|--------------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Color | Natural |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C) |
| Flammability | UL94 V2 (excluding adhesive) |



| Product Selection | | | Length (L) | Width (W) | Height (H) | Pkg. Qty. |
|-------------------|-----------------|--------|------------|-------------|------------|-----------|
| Article No. | Part No. | Type | | | | |
| 151-12820 | TY8H1SH4 | TY8H1S | 1" (26.0) | .90" (23.0) | .75" (6.5) | 500 |


Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Dual Adjustable Flat Ribbon Cable Clamps

Designed to route, protect and secure flat ribbon cables in computers, electronics, panels and components, this unique adjustable clamp will not damage sensitive wire and cable. The clamp will adjust and close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The clamp is releasable on demand and adjustable on both sides. The low profile design allows for use in confined areas where space is a premium.

The clamp is adjustable so that single or stacked cable can be routed. The "snap clamp" design of this flat ribbon cable clamp makes it an excellent choice for specification and installation.

Both adhesive backed and non-adhesive screw mount versions are available.



Material Data

| | |
|-----------------------|---|
| Material | Polyamide 6.6 (PA66) |
| Color | Telecom Gray |
| Operating Temperature | -40 °F to +185 °F (-40 °C to +85 °C) |
| Flammability | UL94 V2 (excluding adhesive) |



Product Selection

| Article No. | Part No. | Type | Length (L) | | Width (W) | | Width (W2) | | Height (H) | | Mounting Hole Ø | | Max Cable Width | | Pkg. Qty. |
|---------------------|-----------------|--------|------------|------|-------------|--------|---------------|---------|--------------|---------|-----------------|-------|-----------------|---------|-----------|
| | | | in. (mm) | (mm) | in. (mm) | (mm) | in. (mm) | (mm) | in. (mm) | (mm) | in. (mm) | (mm) | in. (mm) | (mm) | |
| Adhesive | | | | | | | | | | | | | | | |
| 154-00013 | FC1.2AK2 | FC1.2A | .75" (19) | (19) | 1.5" (38.1) | (38.1) | n/a | n/a | .51" (13.1) | (13.1) | n/a | n/a | 1.2" (30.48) | (30.48) | 50 |
| 154-00012 | FC1.2AH4 | FC1.2A | .75" (19) | (19) | 1.5" (38.1) | (38.1) | n/a | n/a | .51" (12.9) | (12.9) | n/a | n/a | 1.2" (30.48) | (30.48) | 500 |
| 154-00017 | FC2.2AK2 | FC2.2A | .75" (19) | (19) | 2.5" (63.5) | (63.5) | n/a | n/a | .51" (12.75) | (12.75) | n/a | n/a | 2.0" (50.8) | (50.8) | 50 |
| 154-00016 | FC2.2AH4 | FC2.2A | .75" (19) | (19) | 2.5" (63.5) | (63.5) | n/a | n/a | .51" (12.75) | (12.75) | n/a | n/a | 2.0" (50.8) | (50.8) | 500 |
| Non-Adhesive | | | | | | | | | | | | | | | |
| 154-00011 | FC1.2K2 | FC1.2 | .75" (19) | (19) | 1.5" (38.1) | (38.1) | 1.62" (41.15) | (41.15) | .51" (12.9) | (12.9) | .138" (6.0) | (6.0) | 1.2" (30.0) | (30.0) | 50 |
| 154-00010 | FC1.2H4 | FC1.2 | .75" (19) | (19) | 1.5" (38.1) | (38.1) | 1.62" (41.15) | (41.15) | .51" (12.9) | (12.9) | .138" (6.0) | (6.0) | 1.2" (30.0) | (30.0) | 500 |
| 154-00015 | FC2.2K2 | FC2.2 | .75" (19) | (19) | 2.5" (63.5) | (63.5) | 1.5" (38.1) | (38.1) | .51" (12.95) | (12.95) | .138" (6.0) | (6.0) | 2.0" (50.8) | (50.8) | 50 |
| 154-00014 | FC2.2H4 | FC2.2 | .75" (19) | (19) | 2.5" (63.5) | (63.5) | 1.5" (38.1) | (38.1) | .51" (12.95) | (12.95) | .138" (6.0) | (6.0) | 2.0" (50.8) | (50.8) | 500 |


Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Clamps and Clips

Flat Ribbon Cable Clamps

HellermannTyton's flat ribbon cable clamps secure and route flat cable, ideal for automotive and household appliance applications. Available in adhesive backed and non-adhesive screw mount versions.

- Performs well in very dry, air-conditioned areas
- The rounded edges and soft wings protect and hold the cable securely
- Clamps are offered in four sizes that are easy to fasten and unfasten



Material Data

| | |
|-----------------------|---|
| Material | Polyamide 6.6 high impact modified (PA66HIR) |
| Color | Black |
| Operating Temperature | -40 °F to +230 °F (-40 °C to +110 °C) |
| Flammability | UL94 HB (only clamp without adhesive) |




Product Selection

| Article No. | Part No. | Type | Length (L) | Width (W) | Width (W2) | Mounting Hole Ø | | Pkg. Qty. |
|---------------------|------------------|--------|--------------|-------------|-------------|-----------------|----------|-----------|
| | | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| Adhesive | | | | | | | | |
| 151-15250 | 151-15250 | FKH25A | 1.22" (31.0) | .98" (25.0) | .86" (22.0) | n/a | n/a | 100 |
| 151-15300 | 151-15300 | FKH30A | 1.37" (35.0) | .98" (25.0) | .86" (22.0) | n/a | n/a | 100 |
| 151-15500 | 151-15500 | FKH50A | 2.22" (56.6) | .98" (25.0) | .86" (22.0) | n/a | n/a | 100 |
| 151-15800 | 151-15800 | FKH80A | 3.38" (86.0) | .98" (25.0) | .86" (22.0) | n/a | n/a | 100 |
| Non-Adhesive | | | | | | | | |
| 151-16250 | 151-16250 | FKH25 | 1.22" (31.0) | .98" (25.0) | .86" (22.0) | .122" | (3.1) | 100 |
| 151-16300 | 151-16300 | FKH30 | 1.37" (35.0) | .98" (25.0) | .86" (22.0) | .122" | (3.1) | 100 |
| 151-16500 | 151-16500 | FKH50 | 2.22" (56.6) | .98" (25.0) | .86" (22.0) | .122" | (3.1) | 100 |
| 151-16800 | 151-16800 | FKH80 | 3.38" (86.0) | .98" (25.0) | .86" (22.0) | .122" | (3.1) | 100 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Series 13 Ribbon Cable Clamps

Series 13 ribbon cable clips efficiently organize and retain ribbon, flat wire, and flat cable. Easy insertion or removal helps speed installation and control wire runs in almost any location. Series 13 clips offer quick installation with an easy to install adhesive system. 13-0110 clips are suggested for 1-20 conductors. 13-0100 clips are suggested for 20 conductors and larger.



| Material Data | |
|-----------------------|---|
| Material | PVC (Polyvinylchloride) |
| Color | Transparent |
| Operating Temperature | -20 °F to +150 °F (-28 °C to +65 °C) |
| Flammability | UL94 V0 (excluding adhesive) |




| Product Selection | | | | | | |
|-------------------|------------------|---------|------------|---------------|---------------|-----------|
| Article No. | Part No. | Type | Length (L) | Width (W) | Height (H) | Pkg. Qty. |
| | | | in. (mm) | in. (mm) | in. (mm) | |
| 154-00008 | 13-0100K2 | 13-0100 | 1" (25.4) | 1" (25.4) | .391" (9.931) | 50 |
| 154-00001 | 13-0100H4 | 13-0100 | 1" (25.4) | 1" (25.4) | .391" (9.931) | 500 |
| 154-00009 | 13-0110K2 | 13-0110 | 1" (25.4) | .562" (14.30) | .391" (9.931) | 50 |
| 154-00002 | 13-0110H4 | 13-0110 | 1" (25.4) | .562" (14.30) | .391" (9.931) | 500 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Series 42 Wire Routing Clip

The series 42 wire routing clips offer high retention factors for routing small and medium wire and cable. This series easily adapts to routing telephone wire around office desks, can be used for installing security/alarm systems, and holding various types of tubing. The flexible design keeps wire tubing in place.



| Material Data | |
|-----------------------|---|
| Material | PVC (Polyvinylchloride) |
| Color | Transparent |
| Operating Temperature | -20 °F to +150 °F (-28 °C to +65 °C) |
| Flammability | UL94 V0 (excluding adhesive) |



| Product Selection | | | | | | |
|-------------------|------------------|---------|---------------|---------------|---------------|-----------|
| Article No. | Part No. | Type | Max. Ø Bundle | Length (L) | Width (W) | Pkg. Qty. |
| | | | in. (mm) | in. (mm) | in. (mm) | |
| 151-00262 | 42-0010H4 | 42-0010 | .125" (3.18) | 1" (25.4) | 1" (25.4) | 500 |
| 151-00263 | 42-0020H4 | 42-0020 | .188" (4.78) | 1.25" (31.75) | 1" (25.4) | 500 |
| 151-00264 | 42-0030H4 | 42-0030 | .250" (6.35) | 1.5" (38.1) | 1" (25.4) | 500 |
| 151-00265 | 42-0040H4 | 42-0040 | .313" (7.95) | 1.75" (44.45) | 1.25" (31.75) | 500 |
| 151-00266 | 42-0050H4 | 42-0050 | .375" (9.53) | 2" (50.8) | 1.25" (31.75) | 500 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.


Nail Clips

HellermannTyton nail clips are easy to use and highly reliable. The tough, precision engineered clips hold wire and cable securely in place. The nail is hardened for driving into wood, masonry joints, cinder block and mortar. The nails are also perpendicular to the work surface and are driven in straight, greatly reducing cracking. The nail clips do not have sharp edges, which reduce the chance of cutting cable jackets or sheaths and causing signal loss.



Material Data

Material Polyethylene (PE), Steel (ST)



Product Selection

| Article No. | Part No. | Type | Nominal Ø in. (mm) | Length (L) in. (mm) | Application | Color | Pkg. Qty. |
|-------------|----------------|-------|-----------------------|------------------------|---|-------|-----------|
| 148-00005 | NC3.50 | NC3.5 | .138" (3.5) | .630" (16) | 14# Ground Wire, Telecom 1 pair | Black | 100 |
| 148-00006 | NC3.510 | NC3.5 | .138" (3.5) | .630" (16) | | White | 100 |
| 148-00007 | NC50 | NC5 | .197" (5) | .630" (16) | Telecom 4 pair | Black | 100 |
| 148-00008 | NC510 | NC5 | .197" (5) | .630" (16) | | White | 100 |
| 148-00009 | NC60 | NC6 | .236" (6) | .630" (16) | Telecom 6 pair, RG59 | Black | 100 |
| 148-00010 | NC610 | NC6 | .236" (6) | .630" (16) | | White | 100 |
| 148-00011 | NC70 | NC7 | .276" (7) | .787" (20) | RG6 and RG59 Double Shielded | Black | 100 |
| 148-00012 | NC710 | NC7 | .276" (7) | .787" (20) | | White | 100 |
| 148-00013 | NC80 | NC8 | .315" (8) | .787" (20) | Telecom 10 pair RG7, and RG6 Double and Quad Shielded | Black | 100 |
| 148-00014 | NC810 | NC8 | .315" (8) | .787" (20) | | White | 100 |
| 148-00015 | NC90 | NC9 | .354" (9) | .787" (20) | Telecom 12 pair | Black | 100 |
| 148-00016 | NC910 | NC9 | .354" (9) | .787" (20) | | White | 100 |
| 148-00003 | NC110 | NC11 | .433" (11) | .984" (25) | Telecom 25 pair | Black | 100 |
| 148-00004 | NC1110 | NC11 | .433" (11) | .984" (25) | | White | 100 |
| 148-00017 | FC140 | FC14 | .551" (14) | .984" (25) | RG59 and RG6 Flat Twin and Ground | Black | 100 |
| 148-00018 | FC1410 | FC14 | .551" (14) | .984" (25) | | White | 100 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Masonry Clips


Masonry clips are a low cost, easy method for mounting station wire and PBX cable to cinder block, masonry, and other forms of concrete. Two steel pins are molded into them, except for M63-3, which is specially designed with only one pin for routing near corners.




| Material Data | |
|---------------|--------------------|
| Material | Polycarbonate (PC) |
| Color | Transparent |
| Flammability | UL94 V0 |



M63-1



M63-2



M63-3


| Product Selection | | Type | Width (W) | | Width (W2) | | Height (H) | | Pkg. Qty. |
|-------------------|----------------|-------|---------------|---------------|---------------|---------------|---------------|-----|-----------|
| Article No. | Part No. | | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | | |
| 148-00019 | M63-1C2 | M63-1 | .187" (4.75) | .250" (6.35) | .250" (6.35) | .250" (6.35) | .250" (6.35) | 100 | |
| 148-00020 | M63-2C2 | M63-2 | .500" (12.70) | .500" (12.70) | .500" (12.70) | .500" (12.70) | .500" (12.70) | 100 | |
| 148-00021 | M63-3C2 | M63-3 | .500" (12.70) | .500" (12.70) | .500" (12.70) | .500" (12.70) | .500" (12.70) | 100 | |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Siding Clips


All siding clips offer low cost, efficient means of routing and retaining wire on aluminum and vinyl siding. The design eliminates the use of staples, nails, effectively eliminating the problems of corrosion.

All siding clips are compatible with current design of data, CATV and telco wire.



| Material Data - Vertical and Horizontal Siding Clips | | RoHS |
|--|-----------------------------|------|
| Material | Polyamide 6.6 (PA66) | |
| Color | Gray | |
| Flammability | UL94 V2 | |


Vertical Clips - For use with Aluminum Siding



| Product Selection | | | Max. Ø | Width (W) | Length (L) | Height (H) | Height (H2) | Pkg. Qty. |
|-------------------|------------------|---------|------------|---------------|---------------|------------|-------------|-----------|
| Article No. | Part No. | Type | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-00603 | 26-0200M4 | 26-0200 | .24" (6.1) | .733" (18.62) | 1.38" (35.05) | 1" (25.4) | .370" (9.4) | 1000 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Horizontal Clips - For use with Aluminum Siding




| Product Selection | | | Max. Ø | Width (W) | Width (W2) | Length (L) | Pkg. Qty. |
|-------------------|------------------|---------|-------------|--------------|--------------|---------------|-----------|
| Article No. | Part No. | Type | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| 151-00600 | 16-0109M4 | 16-0109 | .10" (2.54) | .368" (9.35) | .230" (5.84) | .780" (19.81) | 1000 |
| 151-00602 | 26-0100M4 | 26-0100 | .24" (6.1) | .500" (12.7) | .370" (9.4) | .830" (21.08) | 1000 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.

Horizontal or Vertical Clips - For use with Aluminum or Vinyl Siding

| Material Data - Telecom Siding Clips | | RoHS |
|--------------------------------------|---------------------------|------|
| Material | Polycarbonate (PC) | |
| Color | Transparent | |
| Flammability | UL94 V0 | |



| Product Selection | | | Width (W) | Length (L) | Length (L2) | Height (H) | Height (H2) | Height (H3) | Pkg. Qty. |
|---|-------------------|----------|--------------|----------------|---------------|--------------|-------------|-------------|-----------|
| Article No. | Part No. | Type | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | in. (mm) | |
| For use with Aluminum Siding - Max. Wire Width - .10" Vertical and .15" Horizontal | | | | | | | | | |
| 151-00601 | 16-0112M4 | 16-0112 | .375" (9.53) | 1.140" (28.96) | .185" (4.7) | .300" (7.62) | .15" (3.81) | .10" (.10) | 1000 |
| For use with Vinyl Siding - Max. Wire Width - .10" Vertical and .15" Horizontal | | | | | | | | | |
| 151-00283 | 16-0112VM4 | 16-0112V | .384" (9.75) | 1.370" (34.8) | .510" (12.95) | .300" (7.62) | .15" (3.81) | .10" (.10) | 1000 |

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.