




Dual Surface Mount Zener Diode



SOT-23

Features:

- SOT-23 Surface Mount Package
- 300mW Power Dissipation Rating
- Ideally Suited for Automatic Insertion
- ΔV_Z for Both Diodes In One Case Is $\leq 5\%$
- Common Cathode Style Available See DZ Series

Absolute Maximum Rating:

$T_A = 25^\circ\text{C}$ unless otherwise specified.

Parameter	Test Conditions	Symbol	Value	Unit
Power dissipation	On fibre glass substrate	P_D	300	mW
Junction and storage temperature range	-	T_j, T_{stg}	-55 to +150	$^\circ\text{C}$

Maximum Thermal Resistance:

$T_j = 25^\circ\text{C}$.

Parameter	Test Conditions	Symbol	Value	Unit
Junction ambient	On fibre glass substrate	R_{thJA}	420	k/W

Maximum Thermal Resistance:


$T_j = 25^\circ\text{C}$.

Part Number	Marking Code	V_Z	Z_{ZT}	Z_{ZK}	T_C	V_R
		V	Ω	Ω	$\%/^\circ\text{C}$	V
		@ $I_{ZT}=5\text{mA}$	@ $I_{ZT}=5\text{mA}$	@ $I_{ZT}=1\text{mA}$		@ $I_R=0.1\mu\text{A}$
AZ23C3V9-7-F	KD5	3.7 to 4.1	95	500	-0.05	-

Dual Surface Mount Zener Diode

Package Outline:


Plastic surface mounted package



SOT-23		
Dim.	Min.	Max.
A	2.85	2.95
B	1.25	1.35
C	1 Typ.	
D	0.37	0.43
E	0.35	0.48
G	1.85	1.95
H	0.02	0.1
J	0.1 Typ.	
K	2.35	2.45

Dimensions : Millimetres

Soldering Footprint:



Dimensions : Millimetres

Package Information:

Device	Package	Shipping
AZ23C3V9-7-F	SOT-23	3,000 / Tape & Reel

Part Number Table

Description	Part Number
300mW Dual Surface Mount Zener Diode	AZ23C3V9-7-F

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.