

**RoHS
Compliant**



Features:

- High efficiency, Low VF
- High current capability
- High reliability
- High surge current capability
- Low power loss

Mechanical Data

Case	: Moulded plastic
Epoxy	: UL 94V-0 rate flame retardant
Polarity	: Colour band denotes cathode
High temperature soldering guaranteed	: 260°C / 10s / 0.375 Inches, (9.5mm) lead lengths at 5 lbs, (2.3kg) tension
Weight	: 0.35 g

Max. Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified
 Single phase, half wave, 60 Hz, resistive or inductive load
 For capacitive load, derate current by 20%

Type Number	Symbol	Values	Unit
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	1,000	V
Maximum RMS Voltage	V _{RMS}	700	
Maximum DC Blocking Voltage	V _{DC}	1,000	
Maximum Average Forward Rectified Current 0.375 Inches (9.5mm) Lead Length at T _A = 75°C	I _{F(AV)}	1	A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load	I _{FSM}	30	
Rating for Fusing (t < 8.3 ms)	I ² T	3.7	A ² S
Maximum Instantaneous Forward Voltage at 1A (Note 1)	V _F	1	V
Maximum Reverse Current at Rated VR T _A = 25°C T _A = 125°C	I _R	5 50	µA
Maximum Full load Reverse Current, Full cycle Average 0.375 Inches (9.5mm) Lead Length at T _A = 75°C	I _{R(AV)}	30	µA
Typical Junction Capacitance (Note 2)	C _J	10	pF
Typical Thermal Resistance	R _{θJA} R _{θJC} R _{θJL}	65 6 15	°C/W
Operating Temperature Range	T _J	-65 to +150	°C
Storage Temperature Range	T _{STG}	-65 to +150	°C

Notes : 1. Pulse Test with PW = 300 usec, 1% Duty Cycle
 2. Measured at 1 MHz and Applied Reverse Voltage of 4 V DC

Rating and Characteristic Curves

Figure 1. Maximum Forward Current Derating Curve







Figure 2. Maximum Non-Repetitive Forward Surge Current




Typical Forward Characteristics



Typical Reverse Characteristics




Typical Junction Capacitance



Dimensions:

1 Amperes Silicon Rectifiers

DO - 41



Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Standard Power Diode, 1A, Single, 2.5V, 30A	1N4007+

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro