PNP High Voltage Transistor







Pin Configuration

- 1. Emitter
- 2. Base
- 3. Collector

Features:

- PNP Silicon High Voltage Transistor
- High speed switching and linear amplifier appliances in Military, Industrial and Commercial Equipment

Absolute Maximum Ratings:

(T_a = 25°C unless otherwise specified)

Characteristic	Symbol	Value	Unit
Collector Base Voltage	V _{CBO}	350	
Collector-Emitter Voltage	V _{CEO}	300	V
Emitter-Base Voltage	V _{EBO}	6	
Collector Current Continuous	I _c	1	^
Base Current	I _B	0.5	A
Power Dissipation at T _a = 25°C Derate above 25°C	Ь	1	W mW/°C
Power Dissipation at T _C = 25°C Derate above 25°C	P _D	10	W
Operating Temperature	T _J	200	mW/°C
Storage Temperature Range	T _{stg}	-65 to +200	°C

Thermal Resistance

Junction to Ambient	R _{th(j-a)}	150	°C/A/
Junction to Case	R _{th(j-c)}	17.5	°C/W

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



PNP High Voltage Transistor



Electrical Characteristics:

 $(T_a = +25^{\circ}C \text{ unless otherwise specified})$

Parameter	Symbol	Test Condition		Unit	
Collector Emitter Breakdown Voltage	BV _{CEO(sus)} *	$I_{\rm C} = 50 {\rm mA}, I_{\rm B} = 0$	>300	V	
Collector Cut off Current	I _{CBO}	V _{CB} = 280V, I _E = 0			
	I _{CEO}	V _{CE} = 250V, I _B = 0	<50	μΑ	
Emitter Cut off Current	I _{EBO}	V _{EB} = 6V, I _C = 0	<20		
Collector Emitter Saturation Voltage	V _{CE(sat)}	I _C = 50mA, I _B = 5mA	<2	\ \	
Base Emitter Saturation Voltage	V _{BE(sat)}	I _C = 50mA, I _B = 5mA	<1.5	V	
DC Current Gain	h _{FE} *	I _C = 50mA, V _{CE} = 10V	30 - 120	-	

Dynamic Characteristics

Small Signal Current Gain	h _{fe}	I _C = 5mA, V _{CE} = 10V, f = 1kHz	>25	-
Transition Frequency	f_T	I _C = 10mA, V _{CE} = 10V, f = 5MHz	>15	MHz
Output Capacitance	C _{ob}	V _{CB} = 10V, I _E = 0, f = 1MHz	<15	
Input Capacitance	C _{ib}	$V_{EB} = V_{EBO}$ max., $I_{C} = 0$, $f = 1MHz$	<75	pF


^{*}Pulsed: Pulse Width ≤30µs, Duty Cycle ≤2%



PNP High Voltage Transistor




TO-39 Metal Can Package



Dim.	Min.	Max.
Α	8.5	9.39
В	7.74	8.5
С	6.09	6.6
D	0.4	0.53
Е	-	0.88
F	2.41	2.66
G	4.82	5.33
Н	0.71	0.86
J	0.73	1.02
K	12.7	-
L	42°	48°

Dimensions: Millimetres



Pin Configuration

- 1. Emitter
- 2. Base
- 3. Collector

Part Number Table

Description	Part Number	
RF Transistor, PNP, TO-39	2N5416	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

