



18V Brushless Rotary Hammer LXT

DHR182ZJ

DHR182 is an 18mm cordless combination hammer powered by 18V LXT Li-ion battery.



TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	18 v
Capacity in Concrete	18 mm
Capacity in Steel	13 mm
Capacity in Wood	24 mm
Max in concrete (TCT core)	35 mm
Max in concrete (Diamond core)	32 mm
Impact energy	1.7 J
Shank	SDS-PLUS
Blows per minute	0 - 5000 bpm
Noise sound pressure	89 dB(A)
Noise sound power	100 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 1,350 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Hammer Drilling	11.0 m/sec ²
Vibration: Chiselling	9.0 m/sec ²

USER BENEFITS

- Brushless motor
- Electric brake
- Variable speed control by trigger
- Constant speed control
- Forward / reverse rotation
- LED job light
- 3x Operating modes (RO/RH/HO)
- Torque limiter
- Anti vibration technology
- Auto-Start Wireless System (AWS) - connects to compatible dust extractors with Bluetooth. The dust extractor automatically runs while the switch is on.
- Depth Gauge
- Ergonomic soft grip
- Compact and lightweight design
- One touch slide chuck for SDS-plus bit.

Link to product - www.makita.com



RELATED PRODUCTS

(Recom

■ STANDARD ACCESSORIES

821552-6

MAKPAC CONNECTOR CASE (TYPE



■ OTHER