

Cable marker - LS-WMTB-V4A (D30) CUS - 0831807

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Cable marker, can be ordered: Piece, silver, labeled according to customer specifications, mounting type: Assembly with cable binders, cable diameter: > 2.9 mm, lettering field size: d 30 mm, Number of individual labels: 20



Your advantages

- Stainless steel cable marking for assembly with cable binders
- High-quality appearance
- Suitable for large-surface marking of conductors and cables > 2.9 mm in diameter

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 930161
GTIN	4046356930161
Weight per Piece (excluding packing)	78.060 g
Custom tariff number	83100000
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	30 mm
Width (a)	30 mm
Material thickness (g)	0.50 mm

Ambient conditions

Ambient temperature (operation)	-80 °C ... 400 °C
---------------------------------	-------------------

General

Color	silver
Type	Card form

Cable marker - LS-WMTB-V4A (D30) CUS - 0831807

Technical data

General

Components	free from silicone, halogen, and cadmium
Material	V4A
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	20
Printability	Direct laser marking
Device	0831831 TOPMARK LASER
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 4.0	EC001530
ETIM 5.0	EC001530

Cable marker - LS-WMTB-V4A (D30) CUS - 0831807

Classifications

ETIM

ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504