

CM-LWN



CM-LWN Motor load monitor, 2x1c/o L1-L2-L3=500VAC, L1/k-L1/l=5A, 110-130VAC

General Information

Extended Product Type	CM-LWN
Product ID	1SVR450330R0000
EAN	4013614347887
Catalog Description	CM-LWN Motor load monitor, 2x1c/o L1-L2-L3=500VAC, L1/k-L1/l=5A, 110-130VAC
Long Description	<p>The CM-LWN relay is from the CM motor load monitors range. This relay operates with a rated control supply voltage of 110-130 V AC, has a 2 x 1 c/o (SPDT) output with contacts rated at 250 V / 4 A and works according to the closed-circuit principle. Its measuring principle is based on the evaluation of the phase shift between the voltage and the current in one phase of single- or three-phase asynchronous motors (squirrel cage). The measuring circuit is designed for measuring voltages of 110-500 V AC and measuring currents of 0.5-5 A AC. The window (over- and underload) monitoring allows setting of two individual threshold values, one for maximum load and one for minimum load. The hysteresis is fixed at 4 ° related to the phase angle. The tripping delay is adjustable within a range of 0.2 to 2 s and the start-up delay within a range of 0.3 to 30 s. A sealable transparent cover for protection against unauthorized changes is available as accessory.</p>

Ordering

EAN	4013614347887
Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Dimensions

Product Net Width	45 mm
Product Net Height	78 mm
Product Net Depth / Length	100 mm
Product Net Weight	0.292 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	81 mm
Package Level 1 Height	106 mm
Package Level 1 Depth / Length	46 mm
Package Level 1 Gross Weight	0.318 kg
Package Level 1 EAN	4013614347887

Technical

Function	Motor load monitoring
Measuring Range	0.5-5 A @ 110-500 V AC
Rated Control Supply Voltage (U _s)	110 ... 130 V AC
Rated Frequency (f)	50 Hz 60 Hz
Output	2 x 1 c/o (SPDT) contact
Time Range	0.3 ... 30 s start-up delay 0.2 ... 2 s tripping delay
Terminal Type	Screw Terminals

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Certificates and Declarations (Document Number)

CB Certificate	CB_DK-8882
CCC Certificate	CCC_2005010303165477
cUL Certificate	cUL508_E140448
Data Sheet, Technical Information	2CDC110004C0209
Declaration of Conformity - CE	1SVD981017-0001
EAC Certificate	EAC_RU_C-DE.ME77.B.01825
Environmental Information	1SAA981003-2403
GL Certificate	GL_96663-95HH
Instructions and Manuals	1SVC450520M0000
RMRS Certificate	RMRS_1740020250
RoHS Information	1SVD981017-0001
UL Certificate	UL508_E140448

Classifications

Object Classification Code	B
ETIM 4	EC002057 - Power relay
ETIM 5	EC002057 - Power relay
ETIM 6	EC002057 - Power relay
ETIM 7	EC002057 - Power relay
eClass	7.0 27371016

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Motor Load Monitors

