


Data Sheet

Type Number 20329
Designation IEC SR731SW
System Silver Oxide / Zinc /
 NaOH - Electrolyte



Nominal Voltage 1,55 V
Typical Capacity C 37 mAh
 Load 20 kOhm, at 20°C down to 1.2 V

Weight (approx.) 0,58 g
Volume 0,15 ccm
Coding..... Date of Manufacturing
 Month/Year



Temperature Ranges min max.
Storage 0°C 60°C
Discharge 0°C 60°C*

Dimensions min max.
Diameter (A) 7,75 7,90
Height (B) 2,85 3,10
Shoulder Diameter[E]..... 3,50
Shoulder Height [C]..... 0,08

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous 24h/d, 7d/w Current [µA]:	20000 Ω	Time: Capacity [mAh]: Energy [mWh]:	495 h 37 55

* Contact VARTA if the application is intended to be outside the range of 0°C to +60°C.

*Information and contents in this data sheet are for reference purpose only.
 They do not constitute any warranty or representation and are subject to change without notice.
 For most current information and further details, please contact your VARTA representative.*