


KEMET, MPXV, Power, 680 nH, 20%

**Dimensions**

L	8.65mm +/-0.25mm
W	8mm +/-0.2mm
T	4mm MAX
LL	1.3mm NOM
G	5.1mm +/-0.3mm

Packaging Specifications

Packaging:	T&R, 330mm
Packaging Quantity:	1000

General Information

Series:	MPXV
Style:	SMD
Description:	Surface Mount Inductor
Features:	Power Inductors
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Core:	Composite
Miscellaneous:	40 (K) Temperature Rise Max.

Specifications

Inductance:	0.68 uH (100 KHz)
Inductance Tolerance:	20%
Temperature Range:	-55/+155°C
Shielded:	Yes
Current:	22.4 A (Irms, 40C Rise By Self Heating), 20.5 A (Isat, 20% Drop In Inductance), 30 A (Isat, 30% Drop In Inductance)
DC Resistance:	3.6 mOhms
Self-Resonant Frequency:	46 MHz