

32-BIT MCU FAMILY

RENESAS RA2A1 GROUP

48MHz ARM Cortex M23 with Integration of 24-bit Sigma Delta ADC

The RA2A1 group uses the high-performance Arm® Cortex®-M23 core and offers highly integrated, high-accuracy analog capabilities and therefore offers complete MCU with analog solution for signal conditioning and measurement. The RA2A1 Group supports a wide operating voltage range of 1.6V to 5.5V. It includes 16-bit SAR ADC, 24-bit Sigma Delta ADC, comparators, operational amplifiers, and DACs. The RA2A1 MCU targets cost sensitive and low power Industrial sensor applications where high resolution analog will become a cost benefit.



RA2A1

48MHz, Arm® Cortex®-M23
256kB Flash, 32kB RAM
32-64pin, USB, CAN, 24bit
Sigma Delta ADC, 16bit ADC,
Security


Target Applications

- Industrial Automation (Photoelectric Sensor, Fiber Sensor, Temperature Sensor)
- Process Automation (Pressure Sensor, Flow control meter, Single Phase Meter)
- Building Automation/Home Appliance (Smoke Detector)
- Healthcare (Pulse Oximeters, Body Composition Measurement)
- General Purpose

Key Features

- 48MHz Arm® Cortex®-M23
- 256kB Flash Memory and 32kB SRAM
- 8kB DataFlash to store data as in EEPROM
- Scalable from 32pin to 64pin Packages
- Capacitive Touch Sensing Unit
- 16bit-SAR A/D, 24bit-SD A/D
- 12bit-D/A, 8bit-D/A
- OPAMP (3ch), ACMP-HS/LP
- USB2.0 Full Speed
- CAN 2.0
- SCI (UART, Simple SPI, Simple I²C)

Block Diagram



RENESAS RA2A1 GROUP

Benefits

- Integrated best-in-class programmable analog for high-accuracy sensor signal acquisition and conditioning.
- Reduce BOM cost and PCB size by eliminating several external analog components.
- Ultra-low power extends battery life for battery-operated portable and battery backup applications.

Tools and Support

Integrated Development Environment (IDE)

- Renesas e² studio
- Keil MDK

Compiler


- GNU, Arm Compiler version 6

Emulator

- Segger J-Link
- Renesas E2 emulator, E2 Lite emulator

Flash Memory Programmer

- Renesas PG-FP6
- Third party solutions



Evaluation Kit

- Full MCU evaluation including On-Chip debugger
 - Part name: RTK7EKA2A1S00001BU



Evaluation Kit: EK-RA2A1

Ordering References

Part name	Flash	RAM	DataFlash	Operating Temperature	Package	Package Dimensions	Pin Pitch
R7FA2A1AB3CFM	256kB	32kB	8kB	-40/+105°C	LQFP 64pin	10x10mm body	0.5mm
R7FA2A1AB3CNE	256kB	32kB	8kB	-40/+105°C	QFN 48pin	7x7mm body	0.5mm
R7FA2A1AB3CNF	256kB	32kB	8kB	-40/+105°C	QFN 40pin	6x6mm body	0.5mm
R7FA2A1AB2CBT	256kB	32kB	8kB	-40/+85°C	BGA 36pin	5x5mm body	0.8mm
R7FA2A1AB3CFJ	256kB	32kB	8kB	-40/+105°C	LQFP 32pin	7x7mm body	0.8mm

For more details, please visit www.renesas.com/RA

renesas.com

Corporate Headquarters
TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks
Arm® and Cortex® are registered trademarks of Arm Limited. Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information
For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/