



Price* : 114.91 GBP



Main

| | |
|----------------------------|--|
| Range of product | Zelio Control |
| Product or component type | Modular measurement and control relays |
| Relay type | Current control relay |
| Relay name | RM35JA |
| Relay monitored parameters | Overcurrent or undercurrent in window mode Overcurrent or undercurrent detection |
| Time delay type | Adjustable 0.1...30 s, +/- 10 % of the full scale value on crossing the threshold Tt |
| Switching capacity in VA | 2000 VA |
| Measurement range | 0.15...1.5 A E1-M terminals 0.5...5 A E2-M terminals 1.5...15 A E3-M terminals 150 mA...15 A current AC/DC 50/60 Hz |

Complementary

| | |
|--------------------------------|--|
| Reset time | 1500 ms at maximum voltage |
| Maximum switching voltage | 250 V AC |
| Minimum switching current | 10 mA at 5 V DC |
| Maximum switching current | 8 A AC |
| [Us] rated supply voltage | 24...240 V AC/DC 50/60 Hz +/- 10 % |
| Supply voltage limits | 20.4...264 V AC/DC |
| Operating limits | - 15 % + 10 % Un |
| Power consumption in VA | 3.5 VA AC |
| Maximum power consumption in W | 1.5 W DC |
| Resistance across terminals | 0.005 Ohm at E3-M terminals 0.015 Ohm at E2-M terminals 0.05 Ohm at E1-M terminals |
| Output contacts | 2 C/O |
| Nominal output current | 8 A |
| Internal input resistance | 0.015 Ohm 0.005 Ohm |

| | |
|---|--|
| | 0.05 Ohm |
| Setting accuracy of the switching threshold | +/- 10 % of the full scale |
| Switching threshold drift | <= 0.05 % per degree centigrade depending permissible ambient air temperature <= 1 % within the supply voltage range |
| Setting accuracy of time delay | 10 P |
| Time delay drift | <= 0.05 % per degree centigrade depending permissible ambient air temperature <= 1 % within the supply voltage range |
| Hysteresis | 5...50 % adjustable of threshold setting for overcurrent or undercurrent detection 3 % fixed of full scale for window mode |
| Run-up delay at power-up | 0.3 s |
| Maximum measuring cycle | 100 ms measurement cycle as true rms value |
| Repeat accuracy | +/- 0.5 % for input and measurement circuit +/- 2 % for time delay |
| Measurement error | < 1 % over the whole range with voltage variation 0.05 %/°C with temperature variation |
| Response time | <= 500 ms (on crossing the threshold) |
| Threshold setting | 10...100 % |
| Overvoltage category | III conforming to IEC 60664-1 III conforming to UL 508 |
| Insulation resistance | > 100 MOhm at 500 V DC conforming to IEC 60255-27 |
| Insulation | Between supply and measurement |
| Mounting position | Any position |
| Connections - terminals | Screw terminals, 2 x 0.5...2 x 2.5 mm ² (AWG 20...AWG 14) solid without cable end Screw terminals, 2 x 0.2...2 x 1.5 mm ² (AWG 24...AWG 16) flexible with cable end Screw terminals, 1 x 0.5...1 x 3.3 mm ² (AWG 20...AWG 12) solid without cable end Screw terminals, 1 x 0.2...1 x 2.5 mm ² (AWG 24...AWG 14) flexible with cable end |
| Tightening torque | 0.6...1 N.m conforming to IEC 60947-1 |
| Housing material | Self-extinguishing plastic |
| Status LED | LED (yellow)relay ON: LED (green)power ON: |
| Mounting support | 35 mm DIN rail conforming to EN/IEC 60715 |
| Electrical durability | 100000 cycles |
| Mechanical durability | 10000000 cycles |
| Utilisation category | AC-15 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1 AC-1 conforming to IEC 60947-4-1 DC-1 conforming to IEC 60947-4-1 |
| Safety reliability data | MTTFd = 296.8 years B10d = 270000 |
| Contacts material | Cadmium free |
| Width | 35 mm |
| Product weight | 0.12 kg |

Environment

| | |
|-------------------------------|--|
| Immunity to microbreaks | 50 ms |
| Electromagnetic compatibility | Immunity for residential, commercial and light-industrial environments conforming to EN/IEC 61000-6-1 Immunity for industrial environments conforming to EN/IEC 61000-6-2 Emission standard for industrial environments conforming to EN/IEC 61000-6-4 Electrostatic discharge - test level: 6 kV level 3 (contact discharge) conforming to IEC 61000-4-2 Electrostatic discharge - test level: 8 kV level 3 (air discharge) conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test - test level: 10 V/m level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test - test level: 4 kV level 4 (direct) conforming to IEC 61000-4-4 Electrical fast transient/burst immunity test - test level: 2 kV level 4 (capacitive coupling) conforming to IEC 61000-4-4 Surge immunity test - test level: 4 kV level 4 (common mode) conforming to IEC 61000-4-5 Surge immunity test - test level: 2 kV level 4 (differential mode) conforming to IEC 61000-4-5 Conducted and radiated emissions class B group 1 conforming to CISPR 11 Conducted and radiated emissions class B conforming to CISPR 22 |

Emission standard for residential, commercial and light-industrial environments (except radiated emission) conforming to EN/IEC 61000-6-3

| | |
|---------------------------------------|--|
| Standards | EN/IEC 60255-1 |
| Product certifications | CE GL CCC EAC RCM China RoHS UL CSA |
| Ambient air temperature for storage | -40...70 °C |
| Ambient air temperature for operation | -20...50 °C at 60 Hz -20...60 °C at 50 Hz AC/DC |
| Environmental characteristic | 3K3 C |
| Relative humidity | 93...97 % at 25...55 °C conforming to IEC 60068-2-30 |
| Vibration resistance | 0.075 mm (f= 10...58.1 Hz) not in operation conforming to IEC 60068-2-6 1 gn (f= 10...58.1 Hz) not in operation conforming to IEC 60068-2-6 0.035 mm (f= 58.1...150 Hz) in operation conforming to IEC 60068-2-6 0.5 gn (f= 58.1...150 Hz) in operation conforming to IEC 60068-2-6 |
| Shock resistance | 15 gn (duration = 11 ms) for not in operation conforming to IEC 60068-2-27 5 gn (duration = 11 ms) for in operation conforming to IEC 60068-2-27 |
| IP degree of protection | IP20 (terminals) conforming to IEC 60529 IP50 (front panel) conforming to IEC 60529 IP30 (housing) conforming to IEC 60529 |
| Pollution degree | 3 conforming to IEC 60664-1 3 conforming to UL 508 |
| Dielectric test voltage | 2.5 kV, 1 min AC 50 Hz conforming to IEC 60255-27 |


Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|


Dimensions



Mounting and Clearance


Rail Mounting

$\frac{\text{mm}}{\text{in.}}$



Current Measurement Relay

Wiring Diagram



A1,A2 : Supply voltage

E1,E2,E3,M : Currents to be measured


11-14,12 : 1st C/O contact of output relay

21-24,22 : 2nd C/O contact of output relay


Function Diagrams

Undercurrent Detection

Without memory ("No Memory" mode)




With memory ("Memory" mode)




Overcurrent Detection

Without memory ("No Memory" mode)



With memory ("Memory" mode)



Legend

- Ti Starting inhibition time delay
- Tt Time delay after crossing of threshold
- Un Supply voltage
- I Monitored current
- H Hysteresis
- I> Overcurrent threshold
- I< Undercurrent threshold
- 11-12/11-14, 21-22/21-24 Output relay connections
- Relay status: black color = energized.

NOTE: In "Memory" mode, the relay opens when crossing of the threshold is detected and then stays in that position. The power supply voltage must be switched off to reset the product.