



Relays, Contactors & Switches > Switches > Switch Knobs



Product Type: **Knob**

Material: **Phenolic**

Knob Design: **Fluted**

Shaft Size: **6.35 mm [.25 in]**

Diameter: **38.1 mm [1.5 in]**

Features

Product Type Features

| | |
|--------------|------|
| Product Type | Knob |
|--------------|------|

Configuration Features

| | |
|-------------|---------|
| Skirt | With |
| Spinner | Without |
| Spin Plate | Without |
| Knob Design | Fluted |

Body Features

| | |
|----------|----------|
| Material | Phenolic |
| Color | Black |

Dimensions

| | |
|------------|-----------------|
| Shaft Size | 6.35 mm[.25 in] |
| Diameter | 38.1 mm[1.5 in] |

Identification Marking

| | |
|--------------------|-------------------|
| Indicator Style | Line |
| Indicator Location | Top, Side & Skirt |

Other

| | |
|---------|-------------------------|
| Comment | Top spun aluminum inlay |
|---------|-------------------------|

Product Compliance



[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | ECHAによる現在の候補リスト: 2019年7月(201) 候補リストの表記: 2018年1月(181) REACH SVHCを含まない |
| EU REACH Regulation (EC) No. 1907/2006 | ECHAによる現在の候補リスト: 2019年7月(201) 候補リストの表記: 2018年1月(181) |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

| | | | |
|---|---|--|---|
|  <p>TE Model / Part #1734595-7 1.0 WTB SR VT HDR 7 POS</p> |  <p>TE Model / Part # YDTS26F21-35PNV001 PLUG ASSY</p> |  <p>TE Model / Part #1059729-1 4584 2240 02</p> |  <p>TE Model / Part #4-1437624-8 PKES150B1/4=KNOB PLSTC FLUTED</p> |
|---|---|--|---|



TE Model / Part #2-1437535-9
510-AG91D-10=INLINE
SOCKET ASS



TE Model / Part #216059-000
55A0111-24-90



TE Model / Part #249943-000
55A0122-22-6/9



TE Model / Part #
YACT20ME35JBV00100
SQUARE FLANGE
RECEPTACLE



TE Model / Part #
YACT20ME35JDV00100
SQUARE FLANGE
RECEPTACLE

Documents

Product Drawings

[PKES140B1/4=KNOB PLSTC FLUTED](#)

English

CAD Files

Customer View Model

[ENG_CVM_4-1437624-7_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_4-1437624-7_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_4-1437624-7_A.2d_dxf.zip](#)

English

3D PDF

English