



1250
LUMEN



4H
RUNTIME



TBC
RANGE



IP65/IPK07
IP RATING

NEW CRI-1250R - RECHARGEABLE HIGH CRI INDUSTRIAL INSPECTION LIGHT

- Super bright 1250 lumen White COB LED
- High CRI 96+ 3 coloured COB LED - CCT range: 2700K / 4500K / 6500K
- Smooth dimming function
- Additional 300 lumen cool white SMD LED top torch
- 5 x UV LEDs on front
- Super tough aluminium and polycarbonate structure
- Strong integral magnets on back and base of light
- Retractable hanging hook in the top
- Glow-in-the-dark strip around LED
- Emergency power-cut activation
- Battery level and charging indicators LEDs
- Built-in power bank for charging devices
- Magnetic charging dock included
- Faster USB Type-C charging - 1m USB cable included

BATTERY 3.7v 5200mAh Li-ion Rechargeable Battery

WEIGHT 406g

DIMENSION 216 x 58 x 38mm



TOP 300 LM FLASHLIGHT



BATTERY & CHARGE INDICATORS