


KEMET, GF, EMI/RFI Filters, Noise Suppression, 250 VAC, 250 V, 5 A



Dimensions	
L	70mm NOM
W	53mm MAX
H	29mm NOM

Packaging Specifications	
Packaging:	Tray, Box
Packaging Quantity:	30
Weight:	130 g

General Information	
Series:	GF
Style:	Metal Box
Description:	Noise Filters
RoHS:	Yes
Qualifications:	UL
Miscellaneous:	30 K Self-Temperature Rise Max

Specifications	
Voltage AC:	250 VAC
Ripple Current:	5 A (AC/DC)
Temperature Range:	-25/+55°C
Voltage:	250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground
Leakage Current:	1 mA MAX (250 V 60 Hz)
Resistance:	300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground