6-1825136-3 ACTIVE

Alcoswitch | Alcoswitch Gemini A

TE Internal #: 6-1825136-3

TE Internal Description: A108SYCQ04

View on TE.com >



Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): Single Pole - Double Throw

Bushing Thread Size: 1/4-40

Sealed: Yes

Contact Base Material: Copper

Switch Contact Plating Material: Silver

Features

Product Type Features

Product Type	Switch
Sealed	Yes
Toggle Style	Baton Long
Switch Type	Toggle
Toggle Actuation	Vertical

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On (On)

Electrical Characteristics

Dielectric Strength	1000 VAC
Insulation Resistance	1000 MΩ
Contact Resistance	10 mΩ
Voltage Rating	20 V

Body Features

Actuator Finish	Nickel
Bushing Thread Size	1/4-40
Seal Type	Terminal Seal (Epoxy)
Bushing Style	Threaded

Contact Features



Contact Base Material	Copper
Switch Contact Plating Material	Silver
Contact Current Rating	5 A
Termination Features	
Termination Type	Printed Circuit
Mechanical Attachment	
Mounting Type	Through Hole
Housing Features	
Process Sealed	No
Dimensions	
Toggle Length	10.4 mm[.41 in]
Industry Standards	
UL Flammability Rating	UL 94V-1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) Pb (3.7% in Component Part)
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts












Also in the Series | Alcoswitch Gemini A




Customers Also Bought





TE Model / Part #1393215-6 V23057-A0002-A201



TE Model / Part #1-2176084-1 EP 7W (S) 470R 5%



TE Model / Part #709836-1 XG7T 16



1825136-8 A101SDCQ04




TE Model / Part #3-1825136-9 A101SDZQ04



TE Model / Part #5-1825137-1 A107SYCQ04



TE Model / Part #4-1623773-2 C10 10R 5% (LOOSE)



1623750-2 ER58 3R3 5% AMMO



TE Model / Part #2-1614353-8 RN 0603 33R2 0.1% 10PPM



TE Model / Part #1624197-4 17P/PC 220KA 6X19FL SPDT PP

Documents

CUT LE

Product Drawings

A108SYCQ04

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

English

Product Environmental Compliance

REACH Substance Communication Document

English