HIGH VOLTAGE POWER OPERATIONAL AMPLIFIERS



PA85 • PA85A 🥯

HTTP://WWW.APEXMICROTECH.COM (800) 546-APEX (800) 546-2739

# **FEATURES**

- HIGH VOLTAGE 450V (±225V)
- HIGH SLEW RATE  $1000V/\mu S$
- HIGH OUTPUT CURRENT 200mA

# **APPLICATIONS**


- HIGH VOLTAGE INSTRUMENTATION
- PIEZO TRANSDUCER EXCITATION
- PROGRAMMABLE POWER SUPPLIES UP TO 430V
- ELECTROSTATIC TRANSDUCERS & DEFLECTION

# DESCRIPTION

The PA85 is a high voltage, high power bandwidth MOS-FET operational amplifier designed for output currents up to 200mA. Output voltages can swing up to ±215V with a dual supply and up to +440 volts with a single supply. The safe operating area (SOA) has no second breakdown limitations and can be observed with all types of loads by choosing an appropriate current limiting resistor. High accuracy is achieved with a cascode input circuit configuration. All internal biasing is referenced to a bootstrapped zener-MOSFET current source. As a result, the PA85 features an unprecedented supply range and excellent supply rejection. The MOSFET output stage is biased on for linear operation. External compensation provides user flexibility.

This hybrid circuit utilizes thick film (cermet) resistors, ceramic capacitors and silicon semiconductor chips to maximize reliability, minimize size and give top performance. Ultrasonically bonded aluminum wires provide reliable interconnections at all operating temperatures. The 8-pin TO-3 package is hermetically sealed and electrically isolated. The use of compressible isolation washers voids the warranty.

# **EQUIVALENT SCHEMATIC**







# TYPICAL APPLICATION

Dynamic focusing is the active correction of focusing voltage as a beam traverses the face of a CRT. This is necessary in high resolution flat face monitors since the distance between cathode and screen varies as the beam moves from the center of the screen to the edges. PA85 lends itself well to this function since it can be connected as a summing amplifier with inputs from the nominal focus potential and the dynamic correction. The nominal might be derived from a potentiometer, or perhaps automatic focusing circuitry might be used to generate this potential. The dynamic correction is generated from the sweep voltages by calculating the distance of the beam from the center of the display.

PACKAGE STYLE CE



# **EXTERNAL CONNECTIONS**



#### **ABSOLUTE MAXIMUM RATINGS**

450V
200mA
30W
±25V
±V <sub>s</sub>
300°C
150°C
–65 to +150°C
–55 to +125°C

# **SPECIFICATIONS**

SPECIFICATIONS									
PARAMETER	TEST CONDITIONS <sup>1</sup>	MIN	PA85 TYP	МАХ	MIN	PA85A TYP	МАХ	UNITS	
INPUT OFFSET VOLTAGE, initial OFFSET VOLTAGE, vs. temperature OFFSET VOLTAGE, vs. supply OFFSET VOLTAGE, vs. time BIAS CURRENT, initial <sup>3</sup> BIAS CURRENT, vs. supply OFFSET CURRENT, initial <sup>3</sup> INPUT IMPEDANCE, DC INPUT CAPACITANCE COMMON MODE VOLTAGE RANGE <sup>4</sup> COMMON MODE REJECTION, DC NOISE	Full temperature range $V_{CM} = \pm 90V$ 100kHz BW, R <sub>s</sub> = 1KΩ, C <sub>c</sub> = 10pf	±V <sub>s</sub> -15 90	.5 10 3 75 5 .01 10 10 <sup>11</sup> 4 110 1	2 30 10 50	* *	.25 5 * 3 * 3 * *	.5 10 * 10 30	mV μV/°C μV//V pA pA/V pA Ω pF V dB μVrms	
GAIN OPEN LOOP, @ 15Hz GAIN BANDWIDTH PRODUCT at 1MHz POWER BANDWIDTH PHASE MARGIN	$\begin{array}{l} \textbf{R}_{L}=2K\Omega, \ \textbf{C}_{c}=\textbf{OPEN}\\ \textbf{R}_{L}=2K\Omega, \ \textbf{C}_{c}=3.3 pf\\ \textbf{C}_{c}=10 pf\\ \textbf{C}_{c}=3.3 pf\\ \textbf{Full temperature range} \end{array}$	96	111 100 300 500 60		*	* * * *		dB MHz kHz kHz °	
OUTPUT VOLTAGE SWING <sup>4</sup> VOLTAGE SWING <sup>4</sup> VOLTAGE SWING <sup>4</sup> CURRENT, continuous SLEW RATE, $A_v = 20$ SLEW RATE, $A_v = 100$ CAPACITIVE LOAD, $A_v = +1$ SETTLING TIME to .1% RESISTANCE, no load	$\begin{split} I_{o} &= \pm 200 \text{mA} \\ I_{o} &= \pm 75 \text{mA} \\ I_{o} &= \pm 20 \text{mA} \\ T_{c} &= 85^{\circ}\text{C} \\ C_{c} &= 10 \text{pf} \\ C_{c} &= \text{OPEN} \\ \text{Full temperature range} \\ Full temperature range \\ C_{c} &= 10 \text{pf}, 2V \text{ step} \\ R_{cL} &= 0 \end{split}$	±V-8.5	±Vs-6.5 ±Vs-6.0 ±Vs-5.5 400 1000 1 50		* * 700 *	* * * * *	*	V V mA V/μs V/μs pf μs Ω	
POWER SUPPLY VOLTAGE <sup>6</sup> CURRENT, quiescent	Full temperature range	±15	±150 21	±225 25	*	*	*	V mA	
THERMAL RESISTANCE, AC, junction to case <sup>5</sup> RESISTANCE, DC, junction to case RESISTANCE, junction to air TEMPERATURE RANGE, case	Full temperature range, F > 60Hz Full temperature range, F < 60Hz Full temperature range Meets full range specifications	-25	30	2.5 4.2 +85	*	*	*	°C/W °C/W °C/W °C	

NOTES: \* The specification of PA85A is identical to the specification for PA85 in applicable column to the left.

1. Unless otherwise noted:  $T_c = 25^{\circ}C$ , compensation =  $C_c = 68pF$ ,  $R_c = 100\Omega$ . DC input specifications are  $\pm$  value given. Power supply voltage is typical rating.

Long term operation at the maximum junction temperature will result in reduced product life. Derate internal power dissipation to achieve high MTTF. Ratings apply only to output transistors. An additional 10W may be dissipated due to quiescent power.

3. Doubles for every 10°C of temperature increase.

4.  $+V_s$  and  $-V_s$  denote the positive and negative power supply rail respectively.

5. Rating applies if the output current alternates between both output transistors at a rate faster than 60Hz.

6. Derate max supply rating .625 V/°C below 25°C case. No derating needed above 25°C case.


# CAUTION

The PA85 is constructed from MOSFET transistors. ESD handling procedures must be observed.

The internal substrate contains beryllia (BeO). Do not break the seal. If accidentally broken, do not crush, machine, or subject to temperatures in excess of 850°C to avoid generating toxic fumes.

# PA85 • PA85A

#### TYPICAL PERFORMANCE GRAPHS



APEX MICROTECHNOLOGY CORPORATION • TELEPHONE (520) 690-8600 • FAX (520) 888-3329 • ORDERS (520) 690-8601 • EMAIL prodlit@apexmicrotech.com

#### OPERATING CONSIDERATIONS

# GENERAL

Please read Application Note 1 "General Operating Considerations" which covers stability, supplies, heat sinking, mounting, current limit, SOA interpretation, and specification interpretation. Visit www.apexmicrotech.com for design tools that help automate tasks such as calculations for stability, internal power dissipation, current limit and heat sink selection. The "Application Notes" and "Technical Seminar" sections contain a wealth of information on specific types of applications. Package outlines, heat sinks, mounting hardware and other accessories are located in the "Packages and Accessories" section. Evaluation Kits are available for most Apex product models, consult the "Evaluation Kit" section for details. For the most current version of all Apex product data sheets, visit www.apexmicrotech.com.

#### **CURRENT LIMIT**

For proper operation, the current limit resistor ( $R_{\rm cL}$ ) must be connected as shown in the external connection diagram. The minimum value is 1.4 ohm, however for optimum reliability the resistor value should be set as high as possible. The value is calculated as follows; with the maximum practical value of 30 ohms.


$$R_{CL} = \frac{.7}{I_{LIM} - .016}$$

# SAFE OPERATING AREA (SOA)

The MOSFET output stage of this power operational amplifier has two distinct limitations:

- 1. The current handling capability of the MOSFET geometry and the wire bonds.
- 2. The junction temperature of the output MOSFETs.

NOTE: The output stage is protected against transient flyback. However, for protection against sustained, high energy flyback, external fast-recovery diodes should be used.



#### SAFE OPERATING CURVES

The safe operating area curves define the maximum additional internal power dissipation the amplifier can tolerate when it produces the necessary output to drive an external load. This is not the same as the absolute maximum internal power dissipation listed elsewhere in the specification since the quiescent power dissipation is significant compared to the total.

#### **INPUT PROTECTION**

Although the PA85 can withstand differential voltages up to  $\pm 25V$ , additional external protection is recommended. Since the PA85 is a high speed amplifier, low leakage, low capacitance JFETs connected as diodes are recommended (e.g. 2N4416, Q1-Q4 in Figure 2). The differential input voltage will be clamped to  $\pm 1.4V$ . This is sufficient overdrive to produce maximum power bandwidth.


#### **POWER SUPPLY PROTECTION**

Unidirectional zener diode transient suppressors are recommended as protection on the supply pins. The zeners clamp transients to voltages within the power supply rating and also clamp power supply reversals to ground. Whether the zeners are used or not, the system power supply should be evaluated for transient performance including power-on overshoot and power-off polarity reversals as well as line regulation.

Conditions which can cause open circuits or polarity reversals on either power supply rail should be avoided or protected against. Reversals or opens on the negative supply rail is known to induce input stage failure. Unidirectional transzorbs prevent this, and it is desirable that they be both electrically and physically as close to the amplifier as possible.

# STABILITY

The PA85 is externally compensated and performance can be tailored to the application. Use the graphs of small signal response and power response as a guide. The compensation capacitor  $C_c$  must be rated at 500V working voltage. An NPO capacitor is recommended. The compensation network  $C_c R_c$  must be mounted closely to the amplifier pins 7 and 8 to avoid spurious oscillation.



This data sheet has been carefully checked and is believed to be reliable, however, no responsibility is assumed for possible inaccuracies or omissions. All specifications are subject to change without notice. PA85U REV N OCTOBER 2006 © 2006 Apex Microtechnology Corp.