SiDR668ADP

www.vishay.com

Vishay Siliconix

N-Channel 100 V (D-S) MOSFET

PowerPAK® SO-8DC

Top View

Bottom View


PRODUCT SUMMARY				
V _{DS} (V)	100			
$R_{DS(on)}$ max. (Ω) at V_{GS} = 10 V	0.0048			
$R_{DS(on)}$ max. (Ω) at V_{GS} = 7.5 V	0.0070			
Q _g typ. (nC)	42			
I _D (A)	104			
Configuration	Single			

FEATURES

- TrenchFET[®] Gen IV power MOSFET
- Very low R_{DS} Q_g figure-of-merit (FOM)
- Tuned for the lowest R_{DS} Q_{oss} FOM
- 100 % R_{q} and UIS tested
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Synchronous rectification
- · Primary side switch
- DC/DC converters
- OR-ing
- Power supplies
- Motor drive control
- Battery and load switch



N-Channel MOSFET

ORDERING INFORMATION				
Package	PowerPAK SO-8DC			
Lead (Pb)-free and halogen-free	SiDR668ADP-T1-RE3			

ABSOLUTE MAXIMUM RATINGS ($T_A = 25 \text{ °C}$, unless otherwise noted)					
PARAMETER		SYMBOL	LIMIT	UNIT	
Drain-source voltage		V _{DS}	100	V	
Gate-source voltage		V _{GS}	± 20	v	
Continuous drain current (T _J = 150 °C)	T _C = 25 °C		104 ^a		
	T _C = 70 °C	·	83 ^a		
	T _A = 25 °C	I _D	23.3 ^{b, c}		
	T _A = 70 °C		18.3 ^{b, c}		
Pulsed drain current (t = 100 µs)		I _{DM}	200	A	
Continuous source-drain diode current	T _C = 25 °C		104		
	T _A = 25 °C	I _S	5.6 ^{b, c}		
Single pulse avalanche current		I _{AS}	35		
Single pulse avalanche energy	L = 0.1 mH	E _{AS}	61.2	mJ	
Maximum power dissipation	T _C = 25 °C		125		
	T _C = 70 °C		80		
	T _A = 25 °C	P _D	6.25 ^{b, c}	W	
	T _A = 70 °C	1	4 b, c		
Operating junction and storage temperature range		T _J , T _{stg}	-55 to +150		
Soldering recommendations (peak temperature) ^{d, e}			260		

Notes

a. Package limited

b. Surface mounted on 1" x 1" FR4 board

c. t = 10 s

d. See solder profile (<u>www.vishay.com/doc?73257</u>). The PowerPAK SO-8 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection

e. Rework conditions: manual soldering with a soldering iron is not recommended for leadless components

(Pb) RoHS

COMPLIANT HALOGEN www.vishay.com

Vishay Siliconix

THERMAL RESISTANCE RATINGS						
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT	
Maximum junction-to-ambient ^a	t ≤ 10 s	R _{thJA}	15	20		
Maximum junction-to-case (drain)	Steady state	R _{thJC}	0.8	1	°C/W	
Maximum junction-to-case (source)	Steady state	R _{thJC}	1.1	1.4		

Notes

a. Surface mounted on 1" x 1" FR4 board

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT	
Static						•	
Drain-source breakdown voltage	V _{DS}	$V_{GS} = 0 V, I_{D} = 250 \mu A$	100	-	-	V	
V _{DS} temperature coefficient	$\Delta V_{DS}/T_{J}$	I _D = 10 mA	-	58	-		
V _{GS(th)} temperature coefficient	$\Delta V_{GS(th)}/T_J$	I _D = 250 μA	-	-9	-	mV/°C	
Gate-source threshold voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_{D} = 250 \ \mu A$	2	-	4	V	
Gate-source leakage	I _{GSS}	$V_{DS} = 0 V, V_{GS} = \pm 20 V$	-	-	100	nA	
Zaus aska valka sa dus'a sumant		V _{DS} = 100 V, V _{GS} = 0 V	-	-	1		
Zero gate voltage drain current	I _{DSS}	V_{DS} = 100 V, V_{GS} = 0 V, T_{J} = 70 °C	-	-	15	μA	
On-state drain current ^a	I _{D(on)}	$V_{DS} \ge 10$ V, V_{GS} =10 V	40	-	-	Α	
Durin country on state mariatemen 3		$V_{GS} = 10 \text{ V}, \text{ I}_{D} = 20 \text{ A}$ $V_{GS} = 7.5 \text{ V}, \text{ I}_{D} = 15 \text{ A}$	-	0.0040	0.0048	Ω	
Drain-source on-state resistance ^a	R _{DS(on)}		-	0.0054	0.0070		
Forward transconductance ^a	g _{fs}	$V_{DS} = 15 \text{ V}, \text{ I}_{D} = 20 \text{ A}$	-	85	-	S	
Dynamic ^b						<u> </u>	
Input capacitance	C _{iss}		-	3750	-	pF	
Output capacitance	Coss	$V_{DS} = 50 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$	-	395	-		
Reverse transfer capacitance	C _{rss}		-	18	-		
Tatal asta abaura	0	$V_{DS} = 50 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 10 \text{ A}$	-	54	81	nC	
Total gate charge	Qg		-	42	63		
Gate-source charge	Q _{gs}	$V_{DS} = 50 \text{ V}, V_{GS} = 7.5 \text{ V}, I_D = 10 \text{ A}$	-	17.5	-		
Gate-drain charge	Q _{gd}		-	11.4	-		
Output charge	Q _{oss}	$V_{DS} = 50 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$	-	73	-		
Gate resistance	R _g	f = 1 MHz	0.3	0.9	1.6	Ω	
Turn-on delay time	t _{d(on)}		-	21	42	-	
Rise time	t _r	$V_{DD} = 50 \text{ V}, \text{ R}_{\text{L}} = 5 \Omega, \text{ I}_{D} \cong 10 \text{ A},$	-	18	36		
Turn-off delay time	t _{d(off)}	$V_{\text{GEN}} = 10 \text{ V}, \text{ R}_{\text{g}} = 1 \Omega$	-	36	72		
Fall time	t _f		-	10	20		
Turn-on delay time	t _{d(on)}		-	25	50	ns	
Rise time	t _r	$V_{DD} = 50 \text{ V}, \text{ R}_{\text{L}} = 5 \Omega, \text{ I}_{D} \cong 10 \text{ A},$	-	61	122	-	
Turn-off delay time	t _{d(off)}	$V_{GEN} = 7.5 \text{ V}, \text{ R}_{g} = 1 \Omega$	-	34	68		
Fall time	t _f		-	11	22		
Drain-Source Body Diode Characteristi	cs						
Continuous source-drain diode current	I _S	T _C = 25 °C	-	-	104	^	
Pulse diode forward current	I _{SM}		-	-	200	A	
Body diode voltage	V _{SD}	$I_{\rm S} = 5$ A, $V_{\rm GS} = 0$ V	-	0.73	1.1	V	
Body diode reverse recovery time	t _{rr}	I _F = 10 A, di/dt = 100 A/μs,	-	59	118	ns	
Body diode reverse recovery charge	Q _{rr}		-	115	230	nC	
Reverse recovery fall time	t _a	$T_{\rm J} = 25 \ ^{\circ}{\rm C}$	-	41	-		
Reverse recovery rise time	t _b		-	18	-	ns	

Notes

a. Pulse test; pulse width \leq 300 µs, duty cycle \leq 2 %


b. Guaranteed by design, not subject to production testing

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


2




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




On-Resistance vs. Drain Current and Gate Voltage




Gate Charge



Transfer Characteristics



Capacitance



On-Resistance vs. Junction Temperature

S19-0906-Rev. A, 28-Oct-2019


3

Document Number: 77245


For technical questions, contact: <u>pmostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage



Single Pulse Power, Junction-to-Ambient



Safe Operating Area, Junction-to-Ambient


S19-0906-Rev. A, 28-Oct-2019

4

For technical questions, contact: <u>pmostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Note


a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?77245.

6



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.