

Equipment marking - EMSP-AL (90X60) - 0830504

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Equipment marking, Aluminum label, aluminum color, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, mounting type: screw, rivet, lettering field size: 90 x 60 mm, Number of individual labels: 1

Your advantages

- Aluminum device marking for screwing or riveting
- The markers can be marked quickly, easily, and inexpensively with the BLUEMARK CLED



Key Commercial Data

Packing unit	15 pc
Minimum order quantity	15 pc
GTIN	 4 046356 719025
GTIN	4046356719025
Weight per Piece (excluding packing)	12.930 g
Custom tariff number	76169990
Country of origin	Germany

Technical data

Dimensions

Length (b)	60 mm
Width (a)	100 mm

Ambient conditions

Ambient temperature (operation)	-55 °C
---------------------------------	--------

General

Color	aluminum color
Components	free from silicone, halogen, and cadmium
Material	Aluminum
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Equipment marking - EMSP-AL (90X60) - 0830504

Technical data

General

Number of individual labels	1
Number of individual labels per row	1
Number of bore holes	4
Printability	UV LED technology
Device	5147999 BLUEMARK CLED
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	screw, rivet

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288

Equipment marking - EMSP-AL (90X60) - 0830504

Classifications

ETIM

ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Magazine

Magazine - BLUEMARK MAG EM-M (100X60) - 0802742



Magazine, width: 76 mm, color: white