

## Plastic label - UC-EMLP (11X9) CUS - 0824547

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: adhesive, lettering field size: 11 x 9 mm



### Your advantages

- ✓ All UC-EMLP ... self-adhesive device markers can also be supplied labeled according to customer requirements
- ✓ Self-adhesive with good adhesive properties
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ Wide temperature range



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 356633
GTIN	4046356356633
Weight per Piece (excluding packing)	6.750 g
Custom tariff number	49119900
Country of origin	Poland
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	9 mm
Width (a)	11 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

#### General

Color	white
-------	-------

# Plastic label - UC-EMLP (11X9) CUS - 0824547

## Technical data

### General

Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels per row	2
Adhesive	Acrylic
Printability	UV LED technology
Device	5147999 BLUEMARK CLED
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Adhesive strength	250 µm
Marking mounting type	adhesive
Result	Test passed
Oxygen index (DIN EN ISO 4589-2)	28,2%
Class I	3
Class F	2
R22	HL 1 - HL 2
R23	HL 1 - HL 2
R24	HL 1 - HL 2

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200

## Plastic label - UC-EMLP (11X9) CUS - 0824547

### Classifications

#### eCl@ss

eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504