

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



N/A = Not Applicable

<b>1. Name of cell / battery</b>
2447-3032-20 4S1P

<b>2. Manufacturer of cell / battery / product</b>	
Name	Ansmann AG
Address	Industriestr. 10, 97959 Assamstadt
Phone	+49 6294 4204-0
Email	info@ansmann.de
Website	www.ansmann.de

<b>3. Test laboratory of cell / battery / product</b>	
Name	Pony Testing International Group
Address	PONY HQ Building:Building 1, No.66 Jindai Road, Zhongguancun Environmental Protection Park
Phone	400-819-5688
Email	pony@ponytest.com
Website	www.ponytest.com

<b>4. ID-number and date</b>			
Unique test report identification number	MDIM2AYU537017A21	Date of test report	12.12.2016

## DESCRIPTION OF CELL / BATTERY

<b>5. Mark the type of cell/battery with an "•"</b>			
<input type="radio"/> Lithium ion cell		Lithium metal cell	<input type="radio"/>
<input checked="" type="radio"/> Lithium ion battery		Lithium metal battery	<input type="radio"/>

<b>6. Parameters</b>	<b>Cell</b>	<b>Battery</b>
Mass in gram (g):		203
Lithium ion: Indicate watt-hour rating (Wh):		51,06
Lithium metal: Indicate lithium metal content in gram (g):		4,83

<b>7. Physical description of cell / battery</b>
Lithium-Ion

# LITHIUM CELL/BATTERY TEST SUMMARY

IN ACCORDANCE WITH SUB-SECTION 38.3  
OF MANUAL OF TESTS AND CRITERIA



<b>Name of cell/battery</b> (taken from field 1)
2447-3032-20 4S1P

<b>8. Model numbers</b>
2447-3032-20; 2447-3032-20-520; 2447-3032-220

## TESTS AND RESULTS

9. List of tests conducted and results - Mark N/A, pass or fail with an "•"	N/A	pass	fail
T1 - Altitude simulation	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T2 - Thermal Test	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T3 - Vibration	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T4 - Shock	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T5 - External Short Circuit	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact / Crush	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T7 - Overcharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T6 - Impact Cell	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>
T8 - Forced Discharge Cell	<input type="radio"/>	<input checked="" type="radio"/>	<input type="radio"/>

<b>10. Reference to assembled battery testing requirements</b>		
Information UN-Test Cell: UN Test Manual of Test and Criteria ST/SG/AC.10/11/Rev.5 Amend.2 ID-number and date QAE-EF02-150313-CY18650MJ1 2015.03.13	N/A	<input type="text"/>

<b>11. Reference to the revised edition of the Manual of Tests and Criteria used and to amendments thereto</b>
ST-SG-AC10-11-Rev.6

**12. The manufacture of the cell / battery is in accordance with the documented quality management system as required by the regulations.**

13. Place, Date	14. Title, Surname, First name	15. Company stamp and signature
Assamstadt	Adrian Selke	Selke, Adrian <small>Digital unterschrieben von Selke, Adrian Datum: 2019.12.02 10:29:03 +01'00'</small>