

Device marker - LS-EMLP-AL (27X27) - 0804298

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Device marker, Aluminum label, aluminum color, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, lettering field size: 27 x 27 mm, Number of individual labels: 30



Your advantages

- Stick-on aluminum device marking



Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 055626 299105
GTIN	4055626299105
Weight per Piece (excluding packing)	88.200 g
Custom tariff number	76169990
Country of origin	China

Technical data

Dimensions

Length (b)	27 mm
Width (a)	27 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C (At temperatures above 80 °C there might be a slight change to the material surface)
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	aluminum color
Components	free from silicone, halogen, and cadmium
Material	Aluminum

Device marker - LS-EMLP-AL (27X27) - 0804298

Technical data

General

RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	30
Adhesive	Acrylic
Printability	Direct laser marking
Device	1012015 TOPMARK NEO
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Note	The information does not apply to the color fastness of the material.
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Procedure	A
Test duration	96 h
Note	The information does not apply to the color fastness of the material.
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Adhesive strength	250 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 5.0	27141100
eCl@ss 5.1	27141137
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

Device marker - LS-EMLP-AL (27X27) - 0804298

Classifications

UNSPSC

UNSPSC 13.2	39131505
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Magazine

Magazine - TOPMARK LASER-MAG SHEET - 0831836

Sheet magazine for TOPMARK LASER



Printing system

Laser marker - TOPMARK NEO SET - 1012018



Laser marker incl. extraction unit, includes operating instructions, declaration of conformity, LS adapter plate, type E and F power cables, LAN cable, D-SUB cable 25-pos., suction tube, crevice nozzle set and filter equipment