

You can view this page in:

EN DE SV FI CS DA EL ES FR HU IT JA KO NL NO PL PT RU SK  
TR ZH

# Detailed information for: TS16/12

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

# TS16/12

## General Information

<b>Extended Product Type:</b>	TS16/12
<b>Product ID:</b>	2CSM228635R0812
<b>EAN:</b>	8012542286356
<b>Catalog Description:</b>	TS16/12 Non-inherently short-circuit proof bell transformer
<b>Long Description:</b>	These transformers with secondary in very low safety voltage for feeding bells are available in 3 series: non-inherently short-circuit proof (TS8), non-inherently short-circuit proof with switch (TS8/SW), non-inherently short-circuit proof (TS16/TS24).

## Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Command and Signalling devices » Bells and safety transformers

## Ordering

<b>EAN:</b>	8012542286356
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85043121

## Dimensions

<b>Product Net Width:</b>	35 mm
<b>Product Net Height:</b>	0.085 m
<b>Product Net Length:</b>	65 mm
<b>Product Net Depth / Length:</b>	0.065 m
<b>Product Net Weight:</b>	0.350 kg

## Container Information

<b>Package Level 1 Units:</b>	6 piece
<b>Package Level 1 Width:</b>	0.09 m
<b>Package Level 1 Height:</b>	0.08 m
<b>Package Level 1 Depth / Length:</b>	0.216 m
<b>Package Level 1 Gross Weight:</b>	2.1 kg
<b>Package Level 1 EAN:</b>	8012542286363

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

## Additional Information

<b>Options Provided:</b>	None
--------------------------	------

<b>Output Current Maximum (<math>I_{out}</math>):</b>	1,33 A
<b>Power Loss:</b>	Maximum 4 W
<b>Power Supply:</b>	16 V·A
<b>Primary Voltage:</b>	230 V
<b>Product Main Type:</b>	TS
<b>Product Name:</b>	Non-inherently short-circuit proof bell transformer
<b>RoHS Date:</b>	25/06/2009 0.00.00
<b>Secondary Voltage:</b>	12 V AC

## Certificates and Declarations (Document Number)

<b>Data Sheet, Technical Information:</b>	<u><a href="#">2CSC000001D0202</a></u>
<b>Declaration of Conformity - CE:</b>	<u><a href="#">2CSC446002D2702</a></u>
<b>Instructions and Manuals:</b>	<u><a href="#">on the product body.</a></u>
<b>RoHS Information:</b>	<u><a href="#">2CSC446004K0201</a></u>

## Classifications

<b>ETIM 4:</b>	EC001547 - Bell transformer
<b>ETIM 5:</b>	EC001547 - Bell transformer
<b>ETIM 6:</b>	EC001547 - Bell transformer
<b>ETIM 7:</b>	EC001547 - Bell transformer
<b>Object Classification Code:</b>	T
<b>WEEE Category:</b>	5. Small Equipment (No External Dimension More Than 50 cm)



## Contact us

Submit your inquiry and  
we will contact you

[CONTACT US](#)

Or contact your [ABB Contact Center](#)