


## Cable marker - WML-RFID/HF 14 (25X19)R - 0803386

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker label with RFID-HF transponder, roll, white, unmarked, can be printed with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X1.2, mounting type: adhesive, min. cable diameter: 9 mm, max. cable diameter: 14 mm, lettering field size: 25 x 19 mm

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 047751
GTIN	4055626047751
Weight per Piece (excluding packing)	499.000 g
Custom tariff number	85235200
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	63 mm
Width (a)	25 mm
Cable diameter	6 mm ... 14 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Recommended storage conditions	20°C/50% relative humidity. Storage in the original packaging is recommended.

#### General

Color	white
Base element material	PVC
Type	Label
Components	Free from silicone and cadmium
Material	PVC

# Cable marker - WML-RFID/HF 14 (25X19)R - 0803386

## Technical data

### General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	750
Number of individual labels per row	1
Adhesive	Acrylic
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	adhesive

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Classifications

### eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

### ETIM

ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

### UNSPSC

UNSPSC 13.2	39131504
-------------	----------

# Cable marker - WML-RFID/HF 14 (25X19)R - 0803386

## Classifications

### UNSPSC

UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

## Approvals

### Approvals

---

Approvals


UL Recognized

---

Ex Approvals

---

### Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE MH 48542
---------------	---	---	---------------

---