

Inline function terminal - IB IL RS 232-2MBD-PAC - 2862084

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Inline RS-232 function terminal block, for serial data transmission, complete with accessories (connector and labeling field), 1 serial input and output channel in RS-232 design


Product Description

The terminal is designed for use within an Inline station. It is used to operate standard I/O devices with serial interfaces on a bus system.

Your advantages

- ✓ One serial RS-232 input and output channel
- ✓ Various protocols supported
- ✓ Transmission speeds can be set up to 38400 Baud
- ✓ Number of data bits, stop bits and parity can be set
- ✓ 4 kbyte receive buffer and 1 kbyte transmit buffer
- ✓ Diagnostic and status indicators

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 974718
GTIN	4017918974718
Weight per Piece (excluding packing)	135.000 g
Custom tariff number	85389091
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	24.4 mm
Height	136.8 mm

Inline function terminal - IB IL RS 232-2MBD-PAC - 2862084

Technical data

Dimensions

Depth	71.5 mm
-------	---------

Connection data

Designation	Inline connector
Connection method	Spring-cage connection
Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section flexible min.	0.08 mm ²
Conductor cross section flexible max.	1.5 mm ²
Conductor cross section AWG min.	28
Conductor cross section AWG max.	16
Stripping length	8 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Degree of protection	IP20

General

Mounting type	DIN rail
Color	green
Net weight	135 g

Interfaces

Designation	Inline local bus
Connection method	Inline data jumper
Transmission speed	2 Mbps
Interface	Serial RS-232
Connection method	Spring-cage connection
Data bits	7 or 8
Stop bits	1 or 2
Input buffer	4 kByte
Output buffer	1 kByte

Inline potentials

Designation	Communications power (U _L)
Supply voltage	7.5 V DC (via voltage jumper)
Current consumption	typ. 165 mA
	max. 225 mA (all connections of the serial interface are short-circuited)

Serial input/output channel

Parity	Even, odd or no parity
--------	------------------------

Inline function terminal - IB IL RS 232-2MBD-PAC - 2862084

Technical data

Serial input/output channel

Transmission type	Transparent mode, end-end mode, dual buffer mode, 3964R, XON/XOFF
-------------------	---

Standards and Regulations


Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


Drawings

Connection diagram



Inline function terminal - IB IL RS 232-2MBD-PAC - 2862084

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27242600
eCl@ss 6.0	27242600
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608
eCl@ss 9.0	27242608

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015

Inline function terminal - IB IL RS 232-2MBD-PAC - 2862084

Classifications

UNSPSC

UNSPSC 12.01	43201404
UNSPSC 13.2	32151602
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

Accessories

Accessories

Connector set

Connector set - IB IL AO/CNT-PLSET - 2732664



Connector set

Labeling panel

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Terminal marking

Insert strip - ESL 62X10 - 0809492

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems: Laser printer, mounting type: insert, lettering field size: 62 x 10 mm, Number of individual labels: 72

