

Warning label - WS PT 6 - 1029029

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Warning label, yellow/black, labeled: Lightning flash, mounting type: plug in, for terminal block width: 8.2 mm

Your advantages

- Mains terminal blocks are reliably covered and marked using warning labels
- Accidental actuation of the terminal points is therefore prevented



Key Commercial Data

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 055626 530420 |
| GTIN | 4055626530420 |
| Weight per Piece (excluding packing) | 1.260 g |
| Custom tariff number | 49119900 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|------------|--------|
| Width (a) | 7.5 mm |
| Height (c) | 8.7 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -60 °C ... 130 °C |
|---------------------------------|-------------------|

General

| | |
|----------------------------------------|--------------------------------|
| Color | yellow/black |
| Type | Rectangle |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V0 |

Warning label - WS PT 6 - 1029029

Technical data

General

| | |
|-----------------------|-----------------------------|
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Printing | Lightning flash |
| Marking mounting type | plug in |

Standards and Regulations

| | |
|----------------------------------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V0 |

Environmental Product Compliance

| | |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 40200103 |
| eCl@ss 4.0 | 40200100 |
| eCl@ss 4.1 | 40200100 |
| eCl@ss 5.0 | 40200100 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 40200100 |
| eCl@ss 7.0 | 40200103 |
| eCl@ss 8.0 | 40200103 |
| eCl@ss 9.0 | 40200103 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001777 |
| ETIM 6.0 | EC001777 |
| ETIM 7.0 | EC001777 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 55121718 |
| UNSPSC 18.0 | 55121718 |
| UNSPSC 19.0 | 55121718 |

Warning label - WS PT 6 - 1029029

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 20.0 | 55121718 |
| UNSPSC 21.0 | 55121718 |