

## Type 2 surge arrester - VAL-MB-T2 1500DC-PV/2+V-FM - 2905646

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Surge arrester for 2-pos. isolated 1500 V DC voltage systems, for DIN rail mounting, with remote indication contact, temperature-monitored protective elements, status message on the module.

### Your advantages

- ✓ Double terminal block for safe and easy equipotential bonding connection
- ✓ Screw shafts with raised domes to ensure safe working
- ✓ Main connections with extended insertion funnels for increased resistance to creepage
- ✓ Visual display for checking the status directly on the device
- ✓ Plug-in signal connection for remote status signaling
- ✓ Compact design for space-saving installation

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 984195
GTIN	4046356984195
Weight per Piece (excluding packing)	389.400 g
Custom tariff number	85354000
Country of origin	Germany

### Technical data

#### Dimensions

Height	120 mm
Width	71.2 mm
Depth	65.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	4 Div.

#### Ambient conditions

Degree of protection	IP20 (only when all terminal points are used)
Ambient temperature (operation)	-40 °C ... 80 °C

# Type 2 surge arrester - VAL-MB-T2 1500DC-PV/2+V-FM - 2905646

## Technical data

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 6000 m (amsl (above mean sea level))
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	50g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (5 - 500 Hz/2.5 h/X, Y, Z)

### General

IEC test classification	PV II
	PV T2
EN type	T2
SPD failure behavior	OCM (Open-circuit mode)
Connection configuration	Y configuration
Installation location	Interior
Accessibility	Accessible
Installation location of the disconnect device	Internal
Mode of protection	(L+) - (L-)
	(L+) - PE
	(L-) - PE
Mounting type	DIN rail: 35 mm
Color	traffic grey A RAL 7042
Housing material	PA 6.6
Degree of pollution	2
Flammability rating according to UL 94	V-0
Type	DIN rail module, one-piece
Surge protection fault message	Optical, remote indicator contact

### Additional descriptions

Note	The product is also suitable for applications in PV systems with a max. short-circuit current $I_{SCPV} = 15 \text{ kA}$ (according to EN 50539-11:2013).
------	---

### Protective circuit DC voltage side (DC)

Maximum continuous operating voltage $U_{CPV}$	1500 V DC
Short-circuit current rating $I_{SCPV}$	2000 A
Continuous operating current $I_{CPV}$	< 55 $\mu\text{A}$
Rated load current $I_L$	50 A
Residual current $I_{PE}$	≤ 55 $\mu\text{A}$ DC
	≤ 430 $\mu\text{A}$ AC
Standby power consumption $P_C$	≤ 85 mVA
Nominal discharge current (8/20) $\mu\text{s}$	20 kA
Maximum discharge current $I_{max}$ (8/20) $\mu\text{s}$	40 kA
Total discharge current $I_{total}$ (8/20) $\mu\text{s}$	40 kA
Voltage protection level $U_p$	≤ 4.5 kV

## Type 2 surge arrester - VAL-MB-T2 1500DC-PV/2+V-FM - 2905646

### Technical data

#### Protective circuit DC voltage side (DC)

Residual voltage $U_{res}$	$\leq 4.5$ kV (at $I_n$ )
	$\leq 3.3$ kV (at 3 kA)
	$\leq 3.6$ kV (at 6.25 kA)
	$\leq 3.8$ kV (at 10 kA)
	$\leq 4.2$ kV (at 15 kA)
	$\leq 5.4$ kV (at 40 kA)
Response time $t_A$	$\leq 25$ ns
Insulation resistance $R_{iso}$	$> 5$ G $\Omega$ (at 500 V DC)

#### Indicator/remote signaling

Switching function	PDT contact
Operating voltage	5 V AC ... 250 V AC
	5 V DC ... 30 V DC
Operating current	5 mA AC ... 1.5 A AC
	5 mA DC ... 1 A DC
Connection method	Screw connection
Screw thread	M2
Tightening torque	0.25 Nm
Stripping length	7 mm
Conductor cross section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section solid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section AWG	28 ... 16

#### Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm
Stripping length	16 mm
Conductor cross section flexible	2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	2.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	10 mm <sup>2</sup>
Conductor cross section AWG	14 ... 2

#### Standards and Regulations

Standards/regulations	EN 50539-11 2013
-----------------------	------------------


#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


# Type 2 surge arrester - VAL-MB-T2 1500DC-PV/2+V-FM - 2905646

## Drawings

Circuit diagram



Dimensional drawing



# Type 2 surge arrester - VAL-MB-T2 1500DC-PV/2+V-FM - 2905646

## Classifications

### eCl@ss

eCl@ss 4.0	27130800
eCl@ss 4.1	27130800
eCl@ss 5.0	27130800
eCl@ss 5.1	27130800
eCl@ss 6.0	27130800
eCl@ss 7.0	27130805
eCl@ss 8.0	27130805
eCl@ss 9.0	27130805

### ETIM

ETIM 3.0	EC000941
ETIM 4.0	EC000941
ETIM 5.0	EC000941
ETIM 6.0	EC000941
ETIM 7.0	EC000941

### UNSPSC

UNSPSC 13.2	39121620
UNSPSC 18.0	39121620
UNSPSC 19.0	39121620
UNSPSC 20.0	39121620
UNSPSC 21.0	39121620

## Approvals

### Approvals

---

#### Approvals

CCA / KEMA-KEUR

---

#### Ex Approvals

---

### Approval details

CCA	NTR-NL 7422
-----	-------------

KEMA-KEUR		<a href="http://www.dekra-certification.com">http://www.dekra-certification.com</a>	2181728.01
-----------	---	---	------------

## Type 2 surge arrester - VAL-MB-T2 1500DC-PV/2+V-FM - 2905646

### Accessories

Accessories

Marker pen

Marker pen - X-PEN 0,35 - 0811228



Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm