

Control box - FL RUGGED BOX DIR-1 - 2701440


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Control box set for constructing wireless systems for industrial applications, incl. panel antenna and 3 m antenna cable for 2.4/5 GHz, IP66, with DIN rail, plugs, and screw connections, with 100 ... 240 V power supply unit, without devices

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 752206
GTIN	4046356752206
Weight per Piece (excluding packing)	1,969.000 g
Custom tariff number	85177000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	174 mm
Height	254 mm
Depth	137 mm

Ambient conditions

Degree of protection	IP66
----------------------	------

Wireless set	Control box (with bore holes incl. sealing plugs, screw connections, and DIN rail), panel antenna incl. antenna cable and 100 ... 240 V AC power supply unit incl. terminal block base
--------------	--

General

Housing material	Polycarbonate
------------------	---------------

Environmental Product Compliance

	Lead 7439-92-1
--	----------------

Control box - FL RUGGED BOX DIR-1 - 2701440

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Articles in set

Antenna - ANT-DIR-2459-01 - 2701186



Directional antenna, 2.4 GHz/5 GHz, gain: 9 dBi, polarization: linear, opening angle: h/v 75°/55°, degree of protection: IP67, seawater-resistant, connection: N (female), incl. mounting bracket and mast clips, ATEX and IECEx approval

Antenna cable - RAD-PIG-RSMA/N-3 - 2903266



Antenna cable, outside diameter: 5 mm (0.2 in.), inner conductor: solid, attenuation: 1.2 / 2.0 / 3.0 dB at 0.9 / 2.4 / 5.8 GHz, connection: N (male) -> RSMA (male), cable length: 3 m (10 ft.)

Power supply unit - STEP-PS/ 1AC/24DC/0.5 - 2868596



Primary-switched STEP POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/0.5 A

Feed-through terminal block - PT 2,5-QUATTRO - 3209578



Feed-through terminal block, nom. voltage: 800 V, nominal current: 24 A, connection method: Push-in connection, number of connections: 4, cross section: 0.14 mm² - 4 mm², AWG: 26 - 12, width: 5.2 mm, height: 35.3 mm, color: gray, mounting type: NS 35/7,5, NS 35/15

Feed-through terminal block - PT 2,5-QUATTRO BU - 3209581



Feed-through terminal block, nom. voltage: 800 V, nominal current: 24 A, connection method: Push-in connection, number of connections: 4, cross section: 0.14 mm² - 4 mm², AWG: 26 - 12, width: 5.2 mm, height: 35.3 mm, color: blue, mounting type: NS 35/7,5, NS 35/15

Control box - FL RUGGED BOX DIR-1 - 2701440

Articles in set

Ground modular terminal block - PT 2,5-QUATTRO-PE - 3209594



Ground modular terminal block, connection method: Push-in connection, number of connections: 4, cross section: 0.14 mm² - 4 mm², AWG: 26 - 12, width: 5.2 mm, height: 35.3 mm, color: green-yellow, mounting type: NS 35/7,5, NS 35/15

RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: PA, connection method: IDC fast connection, connection cross section: AWG 26- 23, cable outlet: straight, color: traffic grey A RAL 7042

Classifications

eCl@ss

eCl@ss 4.0	27240400
eCl@ss 4.1	24010500
eCl@ss 5.0	27144200
eCl@ss 5.1	27144200
eCl@ss 6.0	27144200
eCl@ss 7.0	27144201
eCl@ss 8.0	27180190
eCl@ss 9.0	27180590

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC001358
ETIM 5.0	EC002499
ETIM 6.0	EC001358
ETIM 7.0	EC001358

UNSPSC

UNSPSC 6.01	43172710
UNSPSC 7.0901	43223108
UNSPSC 11	43172710
UNSPSC 12.01	43223108
UNSPSC 13.2	43223108

Control box - FL RUGGED BOX DIR-1 - 2701440

Accessories

Accessories

Mounting material

Mounting material - FL RUGGED BOX POLE SET - 2701205



Set for mast mounting of the FL RUGGED BOX housing, incl. screw clamps for masts up to a diameter of 89 mm

WLAN Ethernet device

Wireless module - FL WLAN 5100 - 2700718



ALTERNATIVE- ARTICLE: FL WLAN 5110 (1043193)

WLAN access point, client, WLAN 802.11 a, b, g, n, frequency 2.4 GHz, 5 GHz, IP20, connections: COMBICON for 10 ...36 V DC, 2x RJ45 for LAN, central cluster management, WBM, 802.11i