

TECHNICAL DATA SHEET

PRO-ELEC

COAXIAL CABLE CB21826 - 827

**RoHS
Compliant**

Part Number	Description	Packaging
CB21826	COAX CABLE RG6U TWIN BLACK 100M	100M/cardboard reel
CB21827	COAX CABLE RG6U TWIN WHITE 100M	100M/cardboard reel

IEC60332-1-2

Construction		
Conductor	Material	Copper clad steel
	Nom O.D. (mm):	1.02±0.01mm
Insulation	Material	Foam PE
	Diameter:	4.57±0.1mm
Screen:		AL.Foil
Braid:	Material	AL/MG
	Size	16X3/0.12±0.003
Sheath:	Material	PVC
	External O.D.	6.5±0.2mm
	Colour:	Black or White

Characteristics at 20°C

Conductor resistance:	≤118.0Ω/km
Insulation resistance:	≥5000MΩ*km
Testing voltage:	wire/wire/screen 50Hz 1min=1.5KV
Impedance:	75±3 Ω at 200Mhz
Capacitance:	53±3 pF/m
Return Loss:	≥20dB
Permissible temperature:	-10°C----70°C

Attenuation

Frequency	50	100	200	800	1000
ATT dB/100m	9.8	11	12.5	18.5	22.5



Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC

TECHNICAL DATA SHEET

Technical Performance (FLUKE Link 90m±3m):

Frequency	RL	ATT	NEXT	DELAY	PSNEXT	ELFEXT	PSELFEX
MHz	≥dB	≤dB	≥dB	≤ns	≥dB	≥dB	≥dTB
1	20.0	2.0	65.3	570.00	62.3	64.0	61.0
4	23.0	4.1	56.3	552.00	53.3	52.0	49.0
8	24.5	5.8	51.8	546.73	48.8	45.9	42.9
10	25.0	6.5	50.3	545.38	47.3	44.0	41.0
16	25.0	8.2	47.2	543.00	44.4	39.9	36.9
20	25.0	9.3	45.8	542.05	42.8	38.0	35.0
25	24.3	10.4	44.3	541.20	41.3	35.8	33.0
31.25	23.6	11.7	42.9	540.44	39.9	34.1	31.1
62.5	21.5	17.0	38.4	538.55	35.4	28.1	25.1
100	20.1	22.0	35.3	537.60	32.3	24.0	21.0