

Cable marker - LS-WMTB-AL (60X15) CUS - 0831788

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, can be ordered: Piece, aluminum color, labeled according to customer specifications, mounting type: Assembly with cable binders, cable diameter: > 4.6 mm, lettering field size: 60 x 15 mm



Your advantages

- ✓ Aluminum cable marking for assembly with cable binders
- ✓ High-quality appearance
- ✓ Suitable for large-surface marking of conductors and cables > 4.6 mm in diameter

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 929905
GTIN	4046356929905
Weight per Piece (excluding packing)	66.740 g
Custom tariff number	83100000
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	78 mm
Width (a)	15 mm
Material thickness (g)	0.80 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C (At temperatures above 80 °C there might be a slight change to the material surface)
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Cable marker - LS-WMTB-AL (60X15) CUS - 0831788

Technical data

General

Color	aluminum color
Type	Card form
Components	free from silicone, halogen, and cadmium
Material	Aluminum
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printability	Direct laser marking
Device	1012015 TOPMARK NEO
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Note	The information does not apply to the color fastness of the material.
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Procedure	A
Test duration	96 h
Note	The information does not apply to the color fastness of the material.
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	Assembly with cable binders

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 4.0	EC001530
ETIM 5.0	EC001530

Cable marker - LS-WMTB-AL (60X15) CUS - 0831788

Classifications

ETIM

ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504