

PRODUCT-DETAILS

A26-30-01 110V 50Hz / 110-120V 60Hz

A26-30-01 110V 50Hz / 110-120V 60Hz

Contactor



General Information

Extended Product Type	A26-30-01 110V 50Hz / 110-120V 60Hz
Product ID	1SBL241001R8401
EAN	3471522061843
Catalog Description	A26-30-01 110V 50Hz / 110-120V 60Hz Contactor
Long Description	A26 contactors are mainly used for controlling 3-phase motors and generally for controlling power circuits up to 690 V AC or 220 V DC. The contactors can also be used for many other applications such as isolation, capacitor switching, lighting. The A... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, 1 built-in auxiliary contact, front and side-mounted add-on auxiliary contact blocks - Control circuit: AC operated with laminated magnet circuit - Accessories: a wide range of accessories is available.

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529

Container Information

Package Level 1 Units	1 piece
-----------------------	---------

Package Level 1 Width	101 mm
Package Level 1 Depth / Length	115 mm
Package Level 1 Height	61 mm
Package Level 1 Gross Weight	0.6 kg
Package Level 1 EAN	3471522061843
Package Level 2 Units	box 24 piece
Package Level 2 Width	300 mm
Package Level 2 Depth / Length	245 mm
Package Level 2 Height	308 mm
Package Level 2 Gross Weight	14.4 kg
Package Level 3 Units	576 piece

Certificates and Declarations (Document Number)

BV Certificate	BV_2634H07559E0
CB Certificate	CB_FR_602227A
CCC Certificate	CCC_2013010304615752 CCC_2004010309133982
CSA Certificate	CSA_1033838_LR056745
Declaration of Conformity - CE	1SBD250801U1000
DNV Certificate	DNV-GL_TAE00000TX
DNV GL Certificate	DNV-GL_TAE00000TX
EAC Certificate	EAC_RU C-FR ME77 B01010
Environmental Information	1SBD250004E1003
GOST Certificate	GOST_POCCFRME77B07175
Instructions and Manuals	FPTC407722P0001
LR Certificate	LRS_9830011E4
RINA Certificate	RINA_ELE128713XG001
RMRS Certificate	RMRS_0507015250
RoHS Information	1SBD250801U1000
UL Certificate	UL_071301E39231

Environmental

Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +55 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +55 °C Close to Contactor without Thermal O/L Relay (Uc) -40 ... +70 °C
Climatic Withstand	acc. to IEC 60068-2-30 and 60068-2-11 - UTE C 63-100 specification II
Maximum Operating Altitude Permissible	3000 m
Resistance to Shock acc. to IEC 60068-2-27	Shock Direction: A 20 K40 Shock Direction: B2 15 K40 Shock Direction: C1 20 K40 Shock Direction: C2 20 K40 Closed, Shock Direction: B1 10 K40 Open, Shock Direction: B1 5 K40
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	3
----------------------------	---

Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 690 V
Rated Frequency (f)	Supply Circuit 50 60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-5-1, $q = 40^\circ\text{C}$ 16 A acc. to IEC 60947-4-1, Open Contactors $q = 40^\circ\text{C}$ 45 A
Rated Operational Current AC-1 (I_e)	(690 V) 40°C 45 A (690 V) 55°C 40 A (690 V) 70°C 32 A
Rated Operational Current AC-3 (I_e)	(220 / 230 / 240 V) 55°C 26 A (380 / 400 V) 55°C 26 A (415 V) 55°C 26 A (440 V) 55°C 26 A (500 V) 55°C 22 A (690 V) 55°C 17 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 6.5 KWT (380 / 400 V) 11 KWT (415 V) 11 KWT (440 V) 15 KWT (500 V) 15 KWT (690 V) 15 KWT
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I_e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I_e AC-3
Rated Operational Current AC-15 (I_e)	(220 / 240 V) 4 A (24 / 127 V) 6 A (380 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Short-Circuit Protective Devices	Auxiliary Circuit - gG Type Fuses 10 A gG Type Fuses 50 A
Maximum Breaking Capacity	$\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 440 V 420 A $\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 690 V 170 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour AC-2 / AC-4 300 cycles per hour AC-3 1200 cycles per hour
Rated Operational Current DC-13 (I_e)	(125 V) 1.1 / 138 A (24 V) 6 / 144 A (250 V) 0.55 / 138 A (48 V) 2.8 / 134 A (72 V) 2 / 144 A
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U_{imp})	8 kV
Mechanical Durability	10 million
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U_c)	50 Hz 110 V 60 Hz 110 ... 120 V
Coil Consumption	Average Holding Value 50 / 60 Hz 12.3 V·A Average Pull-in Value 50 Hz 125 V·A Average Pull-in Value 60 Hz 120 V·A
Operate Time	Between Coil De-energization and NC Contact Closing 7 ... 14 ms Between Coil De-energization and NO Contact Opening 4 ... 11 ms Between Coil Energization and NC Contact Opening 6 ... 18 ms Between Coil Energization and NO Contact Closing 8 ... 21 ms
Connecting Capacity Main Circuit	Flexible with Cable End 0.75 ... 4 m ² Rigid Cable 1.5 ... 6 m ²

Connecting Capacity	Flexible with Cable End 0.75 ... 2.5 mm ²
Auxiliary Circuit	Rigid Cable 1 ... 4 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Connecting Terminals (delivered in open position) Main Poles	M 4 (+,-) pozidriv 2 screws with cable clamp
Terminal Type	Screw Terminals

Dimensions

Product Net Width	54 mm
Product Net Depth / Length	93.6 mm
Product Net Height	90 mm
Product Net Weight	0.6 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100122C0202_Ch02
Instructions and Manuals	FPTC407722P0001

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

