



Relays, Contactors & Switches > Switches > DIP & SIP Switches



Product Type: **Switch**

Contact Mating Area Plating Material: **Gold Flash**

Housing Color: **Black**

Housing Material: **Polyphenylene Sulfide (PPS)**

Auto-Insertable: **Yes**

Features

Product Type Features

Product Type	Switch
Sealed	Yes
Switch Type	DIP
Actuator Style	Flush, Slide

Configuration Features

Number of Positions	5
Number of Switches	5
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Voltage Rating	5 VDC
----------------	-------

Body Features

Seal Type	Tape
Actuator Color	White

Contact Features

	1.2 μ m
Solder Tail Contact Plating	Nickel
Contact Mating Area Plating Material	Gold Flash
Auto-Insertable	Yes
Contact Current Rating	1 A

Contact Base Material	Copper Alloy
-----------------------	--------------

Termination Features

Termination Style	Outside L
-------------------	-----------

Mechanical Attachment

Mounting Type	Surface Mount
---------------	---------------

Housing Features

Housing Color	Black
---------------	-------

Housing Material	Polyphenylene Sulfide (PPS)
------------------	-----------------------------

Centerline	2.54 mm[.1 in]
------------	----------------

Dimensions

Length	14.68 mm[.578 in]
--------	-------------------

Height	3.5 mm[.138 in]
--------	-----------------

Usage Conditions

Operating Temperature Range	-30 – 85 °C
-----------------------------	-------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Packaging Quantity	750
--------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JAN 2018 (181) Does not contain REACH SVHC
--	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JAN 2018 (181)
--	--

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Model / Part # 4-1825059-2
ADF08STTR04=DIP S, FLUSH,SMT-GW



TE Model / Part # 1-1825059-3
ADF04S04=DIP SWT, FLUSH,SMT-GW



TE Model / Part # 1-1825059-8
ADF04STTR04=DIP S, FLUSH,SMT-GW




TE Model / Part # 5-1825059-4
ADF10STTR04=DIP S, FLUSH,SMT-GW


Also in the Series | Alcoswitch DIP



DIP & SIP Switches(256)




Rotary Switches(34)




Switch Boots & Accessories (1)

Also in the Series | Alcoswitch DIP ADF



DIP & SIP Switches(49)

Customers Also Bought

TE Model / Part #2170088-2
ZSFP+ Connector, 15u"TE Model / Part #2007182-1
SFP Standard 1x2 Light
Pipe AssmTE Model / Part #2-
2013290-2
EMBOSS TAPE DDR3
204P 5.2H RVS Au 0.25TE Model / Part #1-
1614882-0
CPF0603 E 0.1% 1K91 1K
RLTE Model / Part #1-
1879135-5
RN 0603 147K 0.1% 10PPM
1K RLTE Model / Part #1825194-1
MSSA135004=SW SLIDE,
SP3T AGTE Model / Part #859527-5
LGH RECEPT., FLANGED,
H.V.TE Model / Part #7-
2176314-5
MELF SMA-A 33R 1%
50PPM 0102 0.3W

Documents

Product Drawings

[ADF05STTR04=DIP S,FLUSH,SMT-GW](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-1825059-4_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-1825059-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1825059-4_A.3d_stp.zip](#)

English



[Datasheets & Catalog Pages](#)

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English