



Relays, Contactors & Switches > Switches > Switch Knobs



Product Type: **Knob**

Material: **Phenolic**

Knob Design: **Straight Knurl with Bar Pointer**

Shaft Size: **6.35 mm [ .25 in ]**

Diameter: **19.3 mm [ .76 in ]**

## Features

### Product Type Features

Product Type	Knob
--------------	------

### Configuration Features

Spin Plate Style	Spun Aluminum
Skirt	Without
Spinner	Without
Spin Plate	With
Knob Design	Straight Knurl with Bar Pointer

### Body Features

Material	Phenolic
Color	Black

### Dimensions

Shaft Size	6.35 mm[.25 in]
Diameter	19.3 mm[.76 in]

### Identification Marking

Indicator Style	Line
Indicator Location	Top & Side

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUN 2018 (191)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Customers Also Bought



TE Model / Part #2118723-4  
STD SHIELD COVER, AL-37.33X34.18X2.00MM



TE Model / Part #2274000-1  
ZSFP+ 1X1 CAGE ASSEMBLY PRESSFIT WITH LP



TE Model / Part #2316531-9  
AV19 SPL 3A MOVING RING R&B 12V




TE Model / Part #3-535542-5  
70 MODIV VRT DR CE 100 /130



TE Model / Part #1571527-1  
[FSM2JSML=TACT  
SWITCH,SMT,BULK](#)



TE Model / Part #2-  
2213819-5  
[6X6 ILL TACT SMT 160GF  
HI BLUE](#)



TE Model / Part #3-  
2154874-2  
[Socket, SCALABLE LED,  
1PC, BRDGLUX ES](#)

## Documents

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_8-1437624-1\\_C\\_c-8-1437624-1-c.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-1437624-1\\_C\\_c-8-1437624-1-c.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_8-1437624-1\\_C\\_c-8-1437624-1-c.3d\\_stp.zip](#)

English