
PRODUCT-DETAILS

CAL5-11

CAL5-11 Auxiliary Contact Block



General Information

Extended Product Type	CAL5-11
Product ID	1SBN010020R1011
EAN	3471522121073
Catalog Description	CAL5-11 Auxiliary Contact Block
Long Description	CAL5-11 Auxiliary Contact Block

Ordering

EAN	3471522121073
Minimum Order Quantity	2 piece
Customs Tariff Number	85389099

Dimensions

Product Net Width	12 mm
Product Net Height	74 mm
Product Net Depth / Length	62 mm
Product Net Weight	0.05 kg

Container Information

Package Level 1 Units	2 piece
Package Level 1 Width	100 mm
Package Level 1 Height	35 mm
Package Level 1 Depth / Length	105.5 mm
Package Level 1 Gross Weight	0.1 kg
Package Level 1 EAN	3471522121073
Package Level 2 Units	box 240 piece
Package Level 2 Width	300 mm
Package Level 2 Height	308 mm
Package Level 2 Depth / Length	245 mm
Package Level 2 Gross Weight	12 kg
Package Level 3 Units	2880 piece

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Additional Information

Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Maximum Electrical Switching Frequency	1200 cycles per hour
Maximum Mechanical Switching Frequency	3600 cycles per hour
Mechanical Durability	10 million 3 million 2 million
Minimum Switching Capacity	A9 ... A75 17 / 5 VLT4K A95 ... AF750 24 / 50 VLT4K
Mounting on Contactors	A 9...A 110
Mounting Position	Side
Mounting Type	Side Mounting
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Order Multiple	2 piece
Power Loss	at Rated Operating Conditions per Pole 0.1 W
Product Main Type	Accessories for Block Contactors
Product Name	Auxiliary Contact Block
Rated Breaking Capacity acc. to IEC 60947-5-1	10 x Ie AC-15
Rated Frequency (f)	Supply Circuit 50 60 Hz
Rated Insulation Voltage (U _i)	acc. to UL/CSA 600 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Making Capacity acc. to IEC 60947-5-1	10 x Ie AC-15
Rated Operational Current AC-15 (I _e)	(220 / 240 V) 4 A (24 / 127 V) 6 A (380 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Rated Operational Current DC-13 (I _e)	(125 V) 0.55 / 69 A (24 V) 6 / 144 A (250 V) 0.3 / 75 A (48 V) 2.8 / 134 A (72 V) 1 / 72 A

Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 24 V
Remarks	100
RoHS Date	2017115
Suitable For	A9 A12 A16 A26 A30 A40 A50 A63 A75 AL9 AL12 AL16 AL26 AL30 AL40 AE45 AE50 AE63 AE75 AF45 AF50 AF63 AF75 TAE45 TAE50 TAE75 UA16 UA26 UA30 UA50 UA63 UA75 UA16RA UA26RA UA30RA UA50RA UA63RA UA75RA GA75 GAE75 N22E N31E N40E N44E N53E N62E N71E N80E N33/11 N51/11 NL22E NL31E NL40E
Technical Information	AUXILIARY SWITCH
Terminal Type	Screw Terminals

Certificates and Declarations (Document Number)

CB Certificate	CB_SE_30113
CCC Certificate	CCC_2013010304604041 CCC_2004010305133985
CSA Certificate	CSA_1033838
Data Sheet, Technical Information	1SBC100122C0202_Ch04
Declaration of Conformity - CE	1SBD250809U1000
EAC Certificate	EAC_RU C-FR ME77 B03391

Environmental Information	1SBD250138E1000
GOST Certificate	GOST_POCCFRME77B07175
Instructions and Manuals	FPTC407744P0001
RINA Certificate	RINA_ELE128713XG001
RoHS Information	1SBD250809U1000
UL Certificate	UL_071301E48139

Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC002498 - Accessories for low-voltage switch technology
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
Object Classification Code	K
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors Accessories

