



Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Round**

Operating Function: **Yes**

Contact Base Material: **Copper Alloy**

Switch Contact Plating Material: **Silver**

Dust Proof: **No**

Features

Product Type Features

Product Type	Switch
Leg Style	Straight
Illuminated	With
Actuator Style	Round
Dust Proof	No

Configuration Features

Tactile Feel	With
ESD Grounding Terminal	Without
Ganged	With
Tactile	Yes
Snap Action	Without
Operating Function	Yes
Support Bracket	Without
Number of Actuators	1

Body Features

Cover Material	Steel
Case Color	Black
Actuator Force	160 g[5.648 oz]
Case Material	Nylon
Bushing Style	Unthreaded

Actuator Profile	Extended
Actuator Material	PBT
Actuator Color	Black

Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver
Contact Current Rating	50 mA

Termination Features

Termination Type	Printed Circuit Board
------------------	-----------------------

Mechanical Attachment

Mounting Type	Through Hole
Mounting Angle	With

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

Actuator Length	9.4 mm[.37 in]
Button Width	3.5 mm[.138 in]
Switch Height	13 mm[.512 in]

Usage Conditions

Temperature Rating	Standard °C
--------------------	-------------

Packaging Features

Packaging Method	Radial Tape
------------------	-------------

Other

Comment	(On) indicates momentary position.
---------	------------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUL 2019 (201)
 Candidate List Declared Against: JAN 2019 (197)
 Does not contain REACH SVHC

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUL 2019 (201)
 Candidate List Declared Against: JAN 2019 (197)

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Model / Part # 1825910-6
 FSM4JH=6MM TACT SWITCH, HIGH TEMP



TE Model / Part # 2-1825910-7
 FSM14JH=6MM TACT SWITCH, HIGH TEMP



TE Model / Part # 4-1437565-2
 FSM4JSMATR=TACT SWITCH 6X6MIL



TE Model / Part # 3-1437565-0
 FSM2JSMATR=ON T/R

Customers Also Bought



TE Model / Part #5535034-4
ASSY,RECEPTACLE,
EUROCARD,TYPE C/2,L-
FREE



TE Model / Part #770087-1
06P .093 COMM P&S
RECPT HSG



TE Model / Part #1-745203-
1
PLUG ASSY,9P,HDE,AP



TE Model / Part #1879353-2
RR02 5% 4K7 AMMO



TE Model / Part #2267078-6
TMS3T5B2M6RE



TE Model / Part #5-102589-
8
12 MODII 2PC HDR DRRR
SHRD, ROHS



TE Model / Part #532956-1
12 MODII 2PC CE RCPT
ASSY



TE Model / Part #532956-8
50 MODII 2PC CE RCPT
ASSY

Documents

Product Drawings

FSM14JRT=SWITCH,TACTILE,RADIAL

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1571010-1_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571010-1_P.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1571010-1_P.2d_dxf.zip](#)

English

3D PDF

3D