

PRODUCT-DETAILS

T5N 400 TMA 400-4000 4p F F InN=100%In

T5N 400 TMA 400-4000 4p F F InN=100%In



General Information

| | |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type | T5N 400 TMA 400-4000 4p F F InN=100%In |
| Product ID | 1SDA054478R1 |
| EAN | 8015644555153 |
| Catalog Description | T5N 400 TMA 400-4000 4p F F InN=100%In |
| Long Description | C.BREAKER TMAX T5N 400 FIXED FOUR-POLE WITH FRONT TERMINALS AND THERMOMAGNETIC RELEASE TMA R 400 I3=2000...4000 A FULLY RATED NEUTRAL |

Ordering

| | |
|------------------------|---------------|
| EAN | 8015644555153 |
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85362090 |

Dimensions

| | |
|----------------------------|----------|
| Product Net Width | 186 mm |
| Product Net Height | 205 mm |
| Product Net Depth / Length | 103.5 mm |
| Product Net Weight | 5.717 kg |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 1 piece |
| Package Level 1 Width | 248 mm |
| Package Level 1 Height | 240 mm |
| Package Level 1 Depth / Length | 285 mm |
| Package Level 1 Gross Weight | 5.8 kg |
| Package Level 1 EAN | 8015644555153 |

Additional Information

| | |
|-------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electrical Durability | 7000 cycle 60 cycles per hour |
| Mechanical Durability | 20000 cycle 120 cycles per hour |
| Number of Poles | 4 |
| Power Loss | at Rated Operating Conditions per Pole 19,5 W |
| Product Main Type | SACE Tmax T |
| Product Name | Moulded Case Circuit Breaker |
| Product Type | CB |
| Rated Current (I_n) | Main Circuit 400 A |
| Rated Impulse Withstand Voltage (U_{imp}) | 8 kV |
| Rated Insulation Voltage (U_i) | 1000 V |
| Rated Operational Voltage | 690 V AC 750 V DC |
| Rated Service Short-Circuit Breaking Capacity (I_{cs}) | (220 V AC) 70 kA (230 V AC) 70 kA (380 V AC) 36 kA (400 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 30 kA (500 V AC) 25 kA (690 V AC) 20 kA |
| Rated Short-time Withstand Current (I_{cw}) | for 1 s 5 kA |
| Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}) | (220 V AC) 70 kA (230 V AC) 70 kA (380 V AC) 36 kA (400 V AC) 36 kA (415 V AC) 36 kA (440 V AC) 30 kA (500 V AC) 25 kA (690 V AC) 20 kA (250 V DC) 2 Poles in Series 36 kA (500 V DC) 2 Poles in Series 25 kA (750 V DC) 3 Poles in Series 16 kA |
| Rated Uninterrupted Current (I_u) | 400 A |
| Release Type | TM |
| Standards | IEC |
| Sub-type | T5 |
| Suitable For | T5 |
| Suitable for Product Class | Moulded Case Circuit Breakers |
| Terminal Connection Type | Fixed Circuit-Breakers Front |
| Test Voltage Max (U_{test}) | 3500 V |
| Test Voltage at Industrial Frequency for 1 Minute | 3500 V |

Version

F

Certificates and Declarations (Document Number)

| | |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1SDC210004D0203 |
| Declaration of Conformity - CE | 1SDL000165R0005 |
| Environmental Information | 1SDL000140R0 |
| Instructions and Manuals | 1SDH000437R0001 |
| Instructions and Manuals (Part 2) | ITSCE-RH0100001 |
| RoHS Information | 1SDL000200R0001 |

Classifications

| | |
|----------------------------|------------------------------------------------------------------------------|
| ETIM 4 | EC000228 - Power circuit-breaker for trafo/generator/installation prot. |
| ETIM 5 | EC000228 - Power circuit-breaker for trafo/generator/installation prot. |
| ETIM 6 | EC000228 - Power circuit-breaker for trafo/generator/installation prot. |
| ETIM 7 | EC000228 - Power circuit-breaker for trafo/generator/installation protection |
| Object Classification Code | Q |
| UNSPSC | 39121100 |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

Categories

Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

