



Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**

Sealed: **Yes**

Contact Base Material: **Copper**

Switch Contact Plating Material: **Silver**

Process Sealed: **No**

Features

Product Type Features

Product Type	Switch
Sealed	Yes
Toggle Style	Baton Long
Switch Type	Toggle
Toggle Actuation	Vertical

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On

Electrical Characteristics

Dielectric Strength	1000 VAC
Insulation Resistance	1000 MΩ
Contact Resistance	10 mΩ
Voltage Rating	125 VAC, 28 VDC

Body Features

Actuator Finish	Nickel
Seal Type	Terminal Seal (Epoxy)
Bushing Style	Unthreaded

Contact Features

Contact Base Material	Copper
-----------------------	--------



Switch Contact Plating Material	Silver
Contact Current Rating	5 A

Termination Features

Termination Type	Printed Circuit
------------------	-----------------

Mechanical Attachment

Mounting Type	Through Hole
---------------	--------------

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	10.4 mm[.41 in] .35 in
---------------	---------------------------

Industry Standards

UL Flammability Rating	UL 94V-1
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) Pb (3.7% in Component Part)
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts




TE Model / Part # 4-1825136-5
A101SYCQ04




TE Model / Part # 4-1825136-9
A101SYZQ04



TE Model / Part # 1825136-7
A101KZQ04



TE Model / Part # 4-1825136-3
A101SYAQ04



TE Model / Part # 5-1825136-9
A108P3ZQ04











Also in the Series | [Alcoswitch Gemini A](#)



Toggle Switches(97)

Customers Also Bought



 TE Model / Part #2-1624112-9 3650 0402 47nH 5% 2K RL	 TE Model / Part #1623894-1 416P 100R	 TE Model / Part #1-1337523-0 BNC Plg Term 50Ohm Nickel Pltd	 TE Model / Part #1-1825137-0 A103SDCB04
 TE Model / Part #1887112-2 XT374L24	 TE Model / Part #5-1879665-4 H8 44K2 0.1% 15PPM	 TE Model / Part #5-1879664-4 H8 4K12 0.1% 15PPM	 TE Model / Part #1-1879363-3 THS75 220R 5%
 TE Model / Part #5-1676914-5 YR1 0.1% 536R	 TE Model / Part #7-1624108-1 3640 0402 20.8nH 2% 1K RL		

Documents

Product Drawings
A101SY9CQ04

English

Datasheets & Catalog Pages
SWITCHES_CORE_PROGRAM_CATALOG

English

GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

English

Product Environmental Compliance
REACH Substance Communication Document

English