

PRODUCT-DETAILS

A145-30-11-80

A145-30-11 220-230V 50Hz / 230-240V 60Hz

Contacteur



General Information

Extended Product Type	A145-30-11-80
Product ID	1SFL471001R8011
EAN	7320500203286
Catalog Description	A145-30-11 220-230V 50Hz / 230-240V 60Hz Contacteur
Long Description	A 3-phase Contacteur suitable for various applications such as Motor starting, Isolation, Bypass and Distribution application up to max 1000 V. Operated with control voltage, versions from 24...690 AC, 50 and 60 Hz

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Norway)	4115096
E-Number (Sweden)	3227854

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	178 mm
Package Level 1 Depth / Length	232 mm
Package Level 1 Height	167 mm
Package Level 1 Gross Weight	3.5 kg
Package Level 1 EAN	7320500203286

Certificates and Declarations (Document Number)

BV Certificate	09826/C0 BV
CB Certificate	SE-69488
CCC Certificate	CQC_2002010304011010
Declaration of Conformity - CE	2CMT2015-005436
DNV Certificate	DNV_E-12191
Environmental Information	1SFC101002D0201
GL Certificate	GL_15529-00HH
Instructions and Manuals	1SFC380003-89
LOVAG Certificate	IT00050
LR Certificate	LR_12-70003
RINA Certificate	ELE060313XG/001
RMRS Certificate	RMRS_12-03683-315
RoHS Information	2CMT2015-005436

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 230 A
Horsepower Rating UL/CSA	(200 V AC) Three Phase 40 hp (208 V AC) Three Phase 40 hp (220 ... 240 V AC) Three Phase 50 hp (440 ... 480 V AC) Three Phase 100 hp (550 ... 600 V AC) Three Phase 125 hp

Environmental

Ambient Air Temperature	Close to Contactor for Storage -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... +50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
Resistance to Shock acc. to IEC 60068-2-27	Shock Direction: A 5 K40 Shock Direction: B1 5 K40 Shock Direction: B2 5 K40 Shock Direction: C1 5 K40 Shock Direction: C2 5 K40

RoHS Status

Following EU Directive 2011/65/EU

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 690 V
Rated Frequency (f)	Main Circuit 50/60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 250 A
Rated Operational Current AC-1 (I_e)	(1000 V) 40 °C 180 A (1000 V) 55 °C 180 A (1000 V) 70 °C 180 A (690 V) 40 °C 250 A (690 V) 55 °C 230 A (690 V) 70 °C 180 A
Rated Operational Current AC-3 (I_e)	(1000 V) 55 °C 80 A (220 / 230 / 240 V) 55 °C 145 A (380 / 400 V) 55 °C 145 A (415 V) 55 °C 145 A (440 V) 55 °C 145 A (500 V) 55 °C 145 A (690 V) 55 °C 120 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 45 KWT (380 / 400 V) 75 KWT (415 V) 75 KWT (440 V) 75 KWT (500 V) 90 KWT (690 V) 110 KWT
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I_e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I_e AC-3
Short-Circuit Protective Devices	gG Type Fuses 315 A
Rated Short-time Withstand Current (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 1200 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 280 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 600 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1800 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 800 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 440 V 1500 A cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 690 V 1200 A
Maximum Electrical Switching Frequency	AC-1 300 cycles per hour AC-2 / AC-4 150 cycles per hour AC-3 300 cycles per hour
Rated Operational Current DC-1 (I_e)	(110 V) 2 Poles in Series, 40 °C 250 A (220 V) 3 Poles in Series, 40 °C 250 A
Rated Operational Current DC-3 (I_e)	(110 V) 2 Poles in Series, 40 °C 250 A (220 V) 3 Poles in Series, 40 °C 250 A
Rated Operational Current DC-5 (I_e)	(110 V) 2 Poles in Series, 40 °C 250 A (220 V) 3 Poles in Series, 40 °C 250 A

Rated Insulation Voltage (U _i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U _{imp})	Main Circuit 8 kV
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	3600 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) 0.85 x U _c Min. ... 1.1 x U _c Max. (at $\theta \leq 70^\circ\text{C}$)
Rated Control Circuit Voltage (U _c)	50 Hz 220 ... 230 V 60 Hz 230 ... 240 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 35 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 40 V·A Pull-in at Max. Rated Control Circuit Voltage 50 Hz 550 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 600 V·A
Operate Time	Between Coil De-energization and NC Contact Closing 5 ... 10 ms Between Coil De-energization and NO Contact Opening 9 ... 13 ms Between Coil Energization and NC Contact Opening 8 ... 22 ms Between Coil Energization and NO Contact Closing 13 ... 27 ms
Connecting Capacity Main Circuit	Bar 24 mm Rigid Al-Cable 1 x 25 ... 150 m ² Rigid Cu-Cable 1 x 6 ... 185 m ²
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1x 0.75 ... 2.5 Flexible with Insulated Ferrule 2x 0.75 ... 2.5 Flexible 2x0.75 ... 2.5 m ² Solid 2 x 1 ... 4 m ² Stranded 2 x 1 ... 4 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Connecting Terminals (delivered in open position) Main Poles	Flat type c/w screws and bolts
Terminal Type	Main Circuit: Bars

Dimensions

Product Net Width	111.5 mm
Product Net Depth / Length	160 mm
Product Net Height	196 mm
Product Net Weight	2.9 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100192C0206
Instructions and Manuals	1SFC380003-89
Dimension Diagram	53540923-7

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900
Replacement Product ID (NEW)	1SFL447002R1311

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

