


PRODUCT-DETAILS

AF265-40-11-13

AF265-40-11-13 Contactor



General Information

Extended Product Type	AF265-40-11-13
Product ID	1SFL547102R1311
EAN	7320500505120
Catalog Description	AF265-40-11-13 Contactor
Long Description	A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, Bypass and Distribution application up to max 1000 V. Operated with wide control voltage range 100-250 V, 50/60 Hz and DC

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
IDEA Granular Category Code (IGCC)	4755 >> Contactors
E-Number (Norway)	4117787
E-Number (Sweden)	3210340

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	212 mm
Package Level 1 Depth / Length	262 mm
Package Level 1 Height	212 mm
Package Level 1 Gross Weight	6.4 kg
Package Level 1 EAN	7320500505120

Certificates and Declarations (Document Number)

ABS Certificate	14-LD1092198-PDA
BV Certificate	BV_36353_A0BV
CB Certificate	SE-89316
CCC Certificate	CQC_2014010304676670
cUL Certificate	20140910-E73397
Declaration of Conformity - CE	2CMT2015-005439
DNV GL Certificate	DNV_E-14043
EAC Certificate	9AKK107046A8618
Instructions and Manuals	1SFC101066M0201
KC Certificate	9AKK107046A9908
LR Certificate	LR_14_70011(E1)
PRS Certificate	TE_2092_880423_16
RINA Certificate	ELE060313XG_002
RMRS Certificate	9AKK107045A6978
RoHS Information	2CMT2015-005439

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
General Use Rating UL/CSA	(600 V AC) 300 A

Environmental

Ambient Air Temperature	Close to Contactor for Storage -40 ... +70 °C Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc) -25 ... +50 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C
Maximum Operating Altitude Permissible	3000 m
RoHS Status	Following EU Directive 2011/65/EU

Technical

Number of Main Contacts	4
NO	

Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	1
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors $q = 40^\circ\text{C}$ 400 A
Rated Operational Current AC-1 (I_e)	(1000 V) 40°C 350 A (1000 V) 60°C 300 A (1000 V) 70°C 240 A (690 V) 40°C 400 A (690 V) 60°C 350 A (690 V) 70°C 290 A
Rated Operational Current AC-3 (I_e)	(220 / 230 / 240 V) 55°C 265 A (380 / 400 V) 55°C 265 A (415 V) 55°C 265 A (440 V) 55°C 265 A
Rated Operational Power AC-3 (P_e)	(220 / 230 / 240 V) 75 KWT (380 / 400 V) 132 KWT (415 V) 132 KWT (440 V) 160 KWT
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I_e AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I_e AC-3
Short-Circuit Protective Devices	gG Type Fuses 630 A
Rated Short-time Withstand Current (I_{cw})	at 40°C Ambient Temp, in Free Air, from a Cold State 10 s 2120 A at 40°C Ambient Temp, in Free Air, from a Cold State 15 min 400 A at 40°C Ambient Temp, in Free Air, from a Cold State 1 min 865 A at 40°C Ambient Temp, in Free Air, from a Cold State 1 s 2650 A at 40°C Ambient Temp, in Free Air, from a Cold State 30 s 1224 A
Maximum Breaking Capacity	$\cos \phi = 0.45$ ($\cos \phi = 0.35$ for $I_e > 100$ A) at 440 V 3800 A
Maximum Electrical Switching Frequency	AC-1 300 cycles per hour
Rated Insulation Voltage (U_i)	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V
Rated Impulse Withstand Voltage (U_{imp})	Main Circuit 8 kV
Mechanical Durability	5 million
Maximum Mechanical Switching Frequency	300 cycles per hour
Coil Operating Limits	(acc. to IEC 60947-4-1) $0.85 \times U_c$ Min. ... $1.1 \times U_c$ Max. (at $\theta \leq 70^\circ\text{C}$)
Rated Control Circuit Voltage (U_c)	50 Hz 100 ... 250 V 60 Hz 100 ... 250 V DC Operation 100 ... 250 V
Coil Consumption	Holding at Max. Rated Control Circuit Voltage 50 Hz 17.5 V·A Holding at Max. Rated Control Circuit Voltage 60 Hz 17.5 V·A Holding at Max. Rated Control Circuit Voltage DC 4.5 W Pull-in at Max. Rated Control Circuit Voltage 50 Hz 385 V·A Pull-in at Max. Rated Control Circuit Voltage 60 Hz 385 V·A Pull-in at Max. Rated Control Circuit Voltage DC 410 W
Operate Time	Between Coil De-energization and NO Contact Opening 45 ... 80 ms

Between Coil Energization and NO Contact Closing 30 ... 60 ms

Connecting Capacity Main Circuit	Flexible 2 x 70 ... 185 m ² Rigid Al-Cable 1 x 185 ... 240 m ² Rigid Cu-Cable 2 x 70 ... 185 m ²
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 2x 0.75 ... 2.5 Flexible with Insulated Ferrule 2x 0.75 ... 2.5 Flexible 2x0.75 ... 2.5 m ² Solid 1 x 1 ... 4 m ² Stranded 2 x 1 ... 4 m ²
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00
Terminal Type	Main Circuit: Bars

Dimensions

Product Net Width	184.4 mm
Product Net Depth / Length	180 mm
Product Net Height	225 mm
Product Net Weight	5.7 kg

Popular Downloads

Data Sheet, Technical Information	1SBC100192C0206
Instructions and Manuals	1SFC101066M0201

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

