

## Section 1 – Chemical Product and Company Identification

Product Name : Polymer Lithium-ion battery  
Details of the Supplier : Premier Farnell plc  
150 Armley Road  
Leeds  
LS12 2QQ  
+44 (0) 8701 202530  
Emergency Telephone : +44 1865 407333

## Section 2 – Hazards Identification

Classification of Danger : See section 14  
Primary Route(s) of Exposure : Eye, skin contact, ingestion.  
Health Hazard : The batteries are not hazardous when used according to the instructions of manufacturer under normal conditions. In case of abuse, there's Hazard of rupture, fire, heat, leakage of internal components, which could cause casualty loss. Abuses including but not limited to the following cases: charged for long time, short circuit, put into fire, whacked with hard object, punctured with acute object, crushed, and broken.

## Section 3 – Composition/Information on Ingredients

Chemical Name	Concentration or concentration ranges (%)	CAS Number
Lithium Cobalt Oxide	20-35	12190-79-3
Graphite	10-25	7782-42-5
Copper Foil	5-15	7440-50-8
Aluminium Foil	5-15	7429-90-5
PVC	1-3	9002-86-2
Electrolyte	10-20	N/A
Other	5-15	N/A

Labelling according to EC directives.  
No symbol and Hazard phrase are required.  
Note: CAS number is Chemical Abstract Service Registry Number.  
N/A=Not apply

## Section 4 – First Aid Measures

Eye : Flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical aid.  
Skin : Remove contaminated clothes and rinse skin with plenty of water or shower for 15 minutes. Get medical aid.  
Inhalation : Remove from exposure and move to fresh air immediately. Use oxygen if available.  
Ingestion : Give at least 2 glasses of milk or water. Induce vomiting unless patient is unconscious. Call a physician.

## Section 5 – Fire Fighting Measures

Characteristics of Hazard	: Dusts at sufficient concentrations can form explosive mixtures with air. Combustion generates toxic fumes.
Hazardous Combustion Products	: Carbon dioxide.
Fire-extinguishing Methods and Extinguishing Media	: For small fires, use water spray, dry chemical, carbon dioxide or chemical foam.
Attention in Fire-extinguishing	: Wear self-contained breathing apparatus in pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## Section 6 – Accidental Release Measures

Personal Precautions, protective equipment, and emergency procedures	: In case of rupture. Attention! Corrosive material. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Refer to protective measures listed in Sections 7 and 8.
Environmental Precautions	: Prevent product from contaminating soil and from entering sewers or waterways.
Methods and materials for Containment	: Stop the leak if safe to do so. Contain the spilled liquid with dry sand or earth. Clean up spills immediately.
Methods and materials for cleaning up	: Absorb spilled material with an inert absorbent (dry sand or earth). Scoop contaminated absorbent into an acceptable waste container. Collect all contaminated absorbent and dispose of according to directions in Section 13. Scrub the area with detergent and water; collect all contaminated wash water for proper disposal.

## Section 7 – Handling and Storage

Handling	: The battery may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity.
Storage	: Store in a cool, dry, well-ventilated area away from incompatible substances. Store locked up. Keep out of the reach of children.
Other Precautions	: In case of rupture. Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Use personal protection equipment.

## Section 8 – Exposure Controls/Personal Protection

Engineering Controls	: Use adequate ventilation to keep airborne concentrations low. If used under conditions that generate particulates, the ACGIH TLV-TWA of 3mg/m <sup>3</sup> respirable fraction (10mg/m <sup>3</sup> total) should be observed.
Personal Protective Equipment	: Eye and Face Protection: None required for consumer use. If there is a Hazard of contact: Tight sealing safety goggles. Face protection shield. Skin and Body Protection: None required for consumer use. If there is a Hazard of contact: Wear protective gloves and protective clothing. Respiratory Protection: No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

## Section 9 – Physical and Chemical Properties

Physical State	: Appearance: Prismatic Colour: Black Odour: If leaking, smells of medical ether.
Change in condition	
pH	: Not applicable as supplied.
Flash Point	: Not applicable unless individual components exposed.
Flammability	: Not applicable unless individual components exposed.
Relative density	: Not applicable unless individual components exposed.
Solubility (water)	: Not applicable unless individual components exposed.
Solubility (other)	: Not applicable unless individual components exposed.

## Section 10 – Stability and Reactivity

Chemical Stability	: Stable under recommended storage conditions.
Possibility of Hazardous Reactions	: None under normal processing.
Conditions to Avoid	: Exposure to air or moisture over prolonged periods.
Incompatible materials	: Acids, Oxidizing agents, Bases.
Hazardous Decomposition Products	: Carbon oxides.

## Section 11 – Toxicological Information

Irritation	: In the event of exposure to internal contents, vapour fumes may be very irritating to the eyes and skin.
Sensitization	: Not Available.
Reproductive Toxicity	: Not Available.
Toxicologically Synergistic Materials	: Not Available.

## Section 12 – Ecological Information

General note	: Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
Anticipated behaviour of a chemical product in environment/possible environmental impact/ ecotoxicity	: Not Available.

## Section 13 – Disposal Considerations

Waste Treatment	: Recycle or dispose of in accordance with government, state & local regulations.
Attention for Waste Treatment	: Deserted batteries shouldn't be treated as ordinary trash. Shouldn't be thrown into fire or placed in high temperature. Shouldn't be dissected, pierced, crushed or treated similarly. Best disposal method is recycling.

## Section 14 – Transport Information

UN number	: 3481
Proper shipping name	: Lithium ion batteries packed with equipment (including lithium ion polymer batteries) or; Lithium ion batteries contained in equipments (including lithium ion polymer batteries).
Class or division	: 9 (Not subject to these Regulations)

Label(s) / Placard Required : Miscellaneous Lithium batt

Special precautions which a user needs to be aware of, or needs to comply with, in connection with transport or conveyance either within or outside their premises

ICAO / IATA : Can be shipped by air in accordance with International Civil Aviation Organization (ICAO), TI or International Air Transport Association (IATA), DGR Packing Instructions (PI) 966 and PI 967 Section II appropriate of IATA DGR 60th (2019 Edition) for transportation.

IMDG CODE : The batteries are not restricted to IMDG Code 2018 Edition (Amdt 39-18) according to special provision 188.

DOT : Other requirements for the US Department of Transportation (DOT) Subchapter C, Hazardous Materials Regulations if shipped in compliance with 49 CFR 173.185.

ADR/ ADN : The batteries are not subject to the provisions of United Nations Economic Commission for Europe (UNECE) ADR/ADN if they meet the requirements of special provision 188 of Chapter 3.3. Applicable as from 1 January 2019.

In addition, to be permitted in transport each lithium cell and battery types must have passed the applicable tests set out in Subsection 38.3 of the UN Manual of Tests and Criteria.

## Section 15 – Regulatory Information

Dangerous Goods Regulations  
Recommendations on the Transport of Dangerous Goods-Model Regulations (20th revised edition)  
Recommendations on the Transport of Dangerous Goods-Manual of Tests and Criteria  
International Air Transport Association (IATA)  
International Maritime Dangerous Goods (IMDG Code 2018 Edition Amdt 39-18)  
Technical Instructions for the Safe Transport of Dangerous Goods  
Classification and code of dangerous goods (GB 6944-2012)  
2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)  
Toxic Substance Control Act (TSCA)  
Code of Federal Regulations  
In accordance with all Federal, State and local laws

## Section 16 – Additional Information

NA

<b>Part Number</b>
MP720417

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.