KERN BALANCES & TEST SERVICES CATALOGUE 2020



Pocket balances KERN TEE · TCB · CM · TGC



KERN TEE

Designer pocket balance at a bargain price



KERN TCB

This is where the fun starts with pocket format weighing



KERN CM

Pocket balance with integrated pocket calculator



KERN TGC

Slim pocket balance with large stainless steel weighing plate and practical tare pan

BATT



OPTION

DAkkS

+3 DAYS

operation







· Simple and convenient 2-key

Cover made of shock proof

used as a tare cup

plastic as protection against

pressure and dust. Can also be



STANDARD

CAL EXT





- operation
- · Transport box and weighing pan included
- · Revolving weighing plate (as overload protection)



OPTION

DAkkS

+3 DAYS











STANDARD

CAL EXT

S

- · Simple and convenient 2-key
- · Small and handy

BATT

- · Simple and convenient 4-key operation
- · Hard case cover as protection against pressure and dust
- Robust, handy, well protected
- Integrated calculator
- · High-resolution pocket balance with particularly rapid reaction and stabilisation time, which means that you can work extremely efficiently
- · Particularly flat design
- · Cover made of shock proof plastic as protection against pressure and dust. Can also be used as a tare cup
- · Stainless steel weighing plate, which makes cleaning easy and hygienic
- · Note: The models are only delivered in a set of 5 units. i.e. the prices given in the table refer to a delivery of 5 items. Cannot be delivered individually. The calibration prices given here refer to calibration of a single balance

Tip: KERN pocket scales are also ideal as a customer gift or for personalized marketing and sales campaigns. We are happy to print your logo on the cover, the lid or the packaging, from 100 pieces. Please inquire details

KERN	TEE 150-1*	TCB 200-1*	CM 60-2N	CM 150-1N	CM 320-1N	CM 1K1N	TGC 150-2S05	TGC 500-1S05	TGC 1K-3S05
Weighing capacity [Max] g	150 g	200 g	60 g	150 g	320 g	1000 g	150 g	500 g	1000 g
Readability [d]	0,1 g	0,1 g	0,01 g	0,1 g	0,1 g	1 g	0,01 g	0,1 g	1 g
LCD display	backlit, digit height 9 mm	digit height 9 mm	backlit, digit height 12 mm				backlit, digit height 12 mm		
Dimensions of weighing plate	W×D 60×64 mm	ø 80 mm	W×D 70×80 mm				ø 81 mm		
Overall dimensions	W×D×H 67×100×22 mm	ø×H 80×14 mm	W×D×H 85×130×25 mm				W×D×H 100×130×18 mm		
Power supply	Batteries included, 2×1,5 V AAA, operating time up to 50 h	Batteries included, 2×LR 44, AUTO-OFF function to preserve battery life	Batteries included, 2×1,5 V AAA, AUTO-OFF function to preserve battery life, operating time up to 33 h				Batteries included, 2× CR2032, operating time up to 33 h		
Net weight	100 g	50 g	180 g				200 g		
Permissible ambient temperature	5 °C/35 °C						0 °C/40 °C		
Option DAkkS Calibr. Certificate	963-127								

KERN BALANCES & TEST SERVICES CATALOGUE 2020

Pictograms



Internal adjusting:

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required



Easy Touch:

Suitable for the connection, data transmission and control through PC, tablet or smartphone



Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



Alibi memory:

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.



Data interface RS-232:

To connect the balance to a printer, PC or network



RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



USB data interface:

To connect the balance to a printer, PC or other peripherals



Bluetooth* data interface:

To transfer data from the balance to a printer, PC or other peripherals



WLAN data interface:

To transfer data from the balance to a printer. PC or other peripherals



Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



Analogue interface:

to connect a suitable peripheral device for analogue processing of the measurements



Interface for second balance:

For direct connection of a second balance




Network interface:

For connecting the scale to an Ethernet network



Wireless data transfer:

between the weighing unit and the evaluation unit using an integrated radio module





KERN Communication Protocol (KCP):

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO log:

The balance displays serial number, user ID, weight, date and time, regardless of a printer connection



GLP/ISO log:

With weight, date and time. Only with KERN printers



Piece counting:

Reference quantities selectable. Display can be switched from piece to weight



Recipe level A:

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



Recipe level B:

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display



Recipe level C:

Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display, multiplier function, adjustment of recipe when dosages are exceeded or barcode recognition



Totalising level A:

The weights of similar items can be added together and the total can be printed out



Percentage determination:

Determining the deviation in % from the target value (100 %)



Weighing units:

Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details



Weighing with tolerance range:

(Checkweighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



MOVE

Hold function:

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram.



Stainless steel:

The balance is protected against corrosion



Suspended weighing:

Load support with hook on the underside of the balance



Battery operation:

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack:

Rechargeable set



Universal mains adapter:

with universal input and optional input socket adapters for A) EU, CH, GB; B) EU, CH, GB, USA; C) EU, CH, GB, USA, AUS



Mains adapter:

230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available



Power supply:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



Weighing principle: Strain gauges

Electrical resistor on an elastic deforming body



Weighing principle: Tuning fork

A resonating body is electromagnetically excited, causing it to oscillate



Weighing principle: Electromagnetic force compensation

Coil inside a permanent magnet. For the most accurate weighings



Weighing principle: Single cell technology:

Advanced version of the force compensation principle with the highest level of precision



Verification possible:

The time required for verification is specified in the pictogram



DAkkS calibration possible:

The time required for DAkkS calibration is shown in days in the pictogram



Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram

KERN - Precision is our business

To ensure the high precision of your balance KERN offers you the the appropriate test weight in the international OIML error limit classes E1-M3 from 1 mg - 2500 kg. In combination with a DAkkS calibration certificate the best pre-requisite for proper

The KERN DAkkS calibration laboratory today is one of the most modern and bestequipped DAkkS calibration laboratories for balances, test weights and force-measure-

Thanks to the high level of automation, we can carry out DAkkS calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

- · DAkkS calibration of balances with a maximum load of up to 50 t
- DAkkS calibration of weights in the range of 1 mg 2500 kg
- · Volume determination and measuring of magnetic susceptibility (magnetic characteristics) for test weights
- · Database supported management of checking equipment and reminder service · Calibration of force-measuring devices
- · DAkkS calibration certificates in the following languages DE, GB, FR, IT, ES, NL, PL
- · Conformity evaluation and reverification of balances and test weights

Your KERN specialist dealer: