



**RoHS
Compliant**



Configurations and Dimensions



Schematic Diagram



Note:
(1) Wire Ø0.3mm × 1P 2UEWF 155°C
(2) 13.5TS (Reference)

Test Data for Mechanical

Test Item	A mm	B mm	C mm	D mm	E mm	F mm	G mm
Specification	12.95 (Max.)	9.5 (Max.)	5.2 (Max.)	8.4 ±0.3	7.62 (Ref.)	2.54 (Ref.)	2.54 (Ref.)
1	12.76	9.21	4.78	8.5	7.62	2.52	2.53
2	12.74	9.22	4.8	8.48	7.6	2.51	2.52
3	12.78	9.21	4.81	8.51	7.61	2.53	2.53
4	12.8	9.18	4.8	8.52	7.62	2.5	2.51
5	12.74	9.19	4.79	8.49	7.59	2.52	2.52
Average	12.76	9.2	4.8	8.5	7.61	2.52	2.52

Electrical Characteristics

Dimensions : Millimetres

Test Condition		
100kHz 0.1V	L	1mH ±10%
at 25°C	DCR	10.3Ω (Max.)
100kHz 0.1V Irms = 0.28A	L at Irms	ΔT 40°C (Max.)

Operating temperature : -55°C to +130°C

Note : Irms : Temperature rise 40°C

Material List



No.	Item	Material Description
1	Core	R5A DR4.8 × 4; R5A RI 8.4 × 4.1 × 6.85
2	Wire	Ø0.3mm × 1P 2UEWF 155°C
3	Solder (Lead Free)	Sn99.3% / Cu0.7%
4	Glue	TH320D / TH320-3
5	Base	SN-BS019.01 LCP

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

Reliability Test

Test Item	Specifications	Test Method and Remarks
Solderability	The electrodes shall be at least 90% covered with new solder coating.	According to IEC68-2-20 Soldering temperature : 245 ±5°C Solder : Sn99.3% / Cu0.7% Flux : Rosin Immersion time : 5 ±1s
Soldering heat resistance	Appearance : No damage Inductance change : Within ±10% of initial value	Preheat temperature 150°C Preheat time : 1 min Solder temperature : 260 ±5°C Dipping time : 10 ±1s Measured at room temperature after placing for 24 hours.
Vibration (Out LAB)	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to MIL-STD202 Method 204 Frequency : 10 to 55 Hz Amplitude : 1.52mm Direction and time X Y and Z direction for 2 hours each.
Humidity resistance test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-1 Method Ca Temperature : 40 ±2°C Humidity : 90%-95% RH Test time : 500 ±2hrs The component should be stabilized at normal condition for 24 hours before test.
High temperature resistance test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-2 Temperature : 85 ±3°C Test time : 500 +24 hrs The component should be stabilized at normal condition for 24 hours before test.
Low temperature resistance test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-1 Method A (Ad) Temperature : -40 ±3°C Test time : 500 +24hrs The component should be stabilized at normal condition for 24 hours before test.
Temperature cycles test	Appearance : No damage All electrical and mechanical parameters within tolerance.	According to IEC68-2-14 Method N (Nb) High-temperature : 85 ±3°C duration 30 mins Room-temperature : 25 ±2°C duration 3 hrs Low-temperature : -40 ±3°C duration 30 mins Room-temperature : 25 ±2°C duration 3 hrs Number of cycle : 10 cycles The component should be stabilized at normal condition for 24 hours before test.

Electric Characteristics



Test Data for Electrical

Test Item	L μH	DCR mΩ	L at Irms μH
Condition	100kHz 0.1V	at 25°C	100kHz 0.1V Irms = 4.08A
Specification	4.7 ±20%	50 (Max.)	ΔT 40°C (Max.)
1	4.63	41.32	OK
2	4.61	41.93	
3	4.64	40.89	
4	4.65	41.56	
5	4.62	41.67	
Average	4.63	41.47	OK

Part Number Table

Description	Part Number
Inductor, 4.7μH, 20%, 3.8A	MCBFS5220-4R7MU

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.