

1248AS-H-330M#

indicates a package specification code.

In Production
General
85 °C max. (Ferrite)
Wound (Ferrite)
Reflow OK
RoHS
REACH

< List of part numbers with package codes >
1248AS-H-330M=P3

Shape

L size	8.0 ±0.3mm
W size	8.0 ±0.3mm
T size	4.0 mm
Size code in inch (mm)	3131 (8080)

Notes

Rated current (I_{sat}) is specified when the decrease of the initial inductance value at 30%.
Rated current (I_{temp}) is specified when temperature of the inductor is raised 40 °C by DC current.

References

Packaging code	Specifications	Minimum quantity
=P3	φ330mm Embossed taping	1000




Mass (Typ.)	
1 piece	1.05g

Specifications

Inductance	33μH ±20%
Inductance test frequency	0.1MHz
Rated current (I _{sat}) (Based on Inductance change)	2400mA
Rated current (I _{temp}) (Based on Temperature rise)	1800mA
Max. of DC resistance	0.168Ω
Avg. of DC resistance	0.1400Ω ±20%
Operating temperature range (Self-temperature rise is included)	-40 to 85°C
Class of magnetic shield	Ferrite Core
Series	DEM8040C

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.