

## Electronic housing - EMG 22-B4 - 2946146

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Custom circuit module, consisting of housing, MKDS 3 connection terminal blocks and PCB

### Your advantages

- ✓ Choice of four cover sizes in transparent or color versions
- ✓ Practical and easy-to-wire conductor connections
- ✓ Uniform and appropriate housing technology
- ✓ High degree of flexibility due to the wide choice of versions
- ✓ Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- ✓ User-friendly and safe mounting on DIN rails according to EN 60715
- ✓ Inflammability class V0 insulation material (according to UL 94)
- ✓ Shock and contamination-proof accommodation of electronic components
- ✓ Universal PCBs for all pitches

### Key Commercial Data

|                                      |               |
|--------------------------------------|---------------|
| Packing unit                         | 10 pc         |
| GTIN                                 |               |
| GTIN                                 | 4017918082109 |
| Weight per Piece (excluding packing) | 44.010 g      |
| Custom tariff number                 | 85369010      |
| Country of origin                    | Germany       |

### Technical data

#### General

|                  |                                |
|------------------|--------------------------------|
| Housing type     | Component housing              |
| Housing material | Polycarbonate fiber reinforced |
| Color (RAL)      | green                          |

#### Ambient conditions

# Electronic housing - EMG 22-B4 - 2946146

## Technical data

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

### Dimensions

|        |         |
|--------|---------|
| Length | 75 mm   |
| Height | 47.5 mm |
| Width  | 22.5 mm |
| Pitch  | 5 mm    |
| Depth  | 75 mm   |

### Technical data

|                                  |       |
|----------------------------------|-------|
| Power dissipation without gap    | 1.4 W |
| Power dissipation with 20 mm gap | 1.6 W |
| Number of positions              | 8     |

### Standards and Regulations


|  |    |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

### Environmental Product Compliance

|            |   |
|------------|---|
|            | Lead 7439-92-1  |
| China RoHS | Environmentally Friendly Use Period = 50  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Drawings

Dimensional drawing




1 = Top edge of the PCB

# Electronic housing - EMG 22-B4 - 2946146

B = Housing width

Dimensional drawing



Pitch 5 mm

a = Area for mounting components, 38 mm in the hood

b = Area for mounting components, 45 mm in the housing

## Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27180400 |
| eCl@ss 4.1 | 27180400 |
| eCl@ss 5.0 | 27180500 |
| eCl@ss 5.1 | 27180500 |
| eCl@ss 6.0 | 27180800 |
| eCl@ss 7.0 | 27182702 |
| eCl@ss 8.0 | 27182702 |
| eCl@ss 9.0 | 27182702 |

ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001031 |
| ETIM 3.0 | EC001031 |
| ETIM 4.0 | EC001031 |
| ETIM 5.0 | EC001031 |
| ETIM 6.0 | EC001031 |
| ETIM 7.0 | EC001031 |

# Electronic housing - EMG 22-B4 - 2946146

## Classifications

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261501 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11     | 31261501 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 31261501 |
| UNSPSC 18.0   | 31261501 |
| UNSPSC 19.0   | 31261501 |
| UNSPSC 20.0   | 31261501 |
| UNSPSC 21.0   | 31261501 |

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

|     |  |         |
|-----|--|---------|
| EAC |  | B.01742 |
|-----|--|---------|

## Accessories

### Accessories

### Device marking

Marking material - EMG-GKS 22 - 2941594



Device marking label, width: 22 mm, area: 22 x 8 mm, e.g. for EML(20x8) R adhesive marking material

### Filler plug

---

## Electronic housing - EMG 22-B4 - 2946146

### Accessories

Electronic housing - EMG-KA - 2941510



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

---

Marking material - EMG-GKS 12 - 2947035



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

---

Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

---

### Necessary add-on products

Covering hood - EMG 22-H 7,5MM KLAR - 2946159



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm, width: 22.5 mm

---

Covering hood - EMG 22-H 15MM KLAR - 2946162



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 22.5 mm

---

## Electronic housing - EMG 22-B4 - 2946146

### Accessories

Covering hood - EMG 22-H 35MM KLAR - 2942771



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 35 mm, width: 22.5 mm

---

Covering hood - EMG 22-H 52MM GN - 2946175



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 22.5 mm

---

---